



A.



Indoor Steel Enclosure

Type 1 Enclosure

- Drawn steel with gray powder coat paint finish
- Combination 1/2" and 3/4" nominal knockouts with one on back and each side of enclosure, and two on bottom
- Convenient mounting holes
- Lockable hasp holds door closed

Model #	Color	H x W x D
A. 2T2040GA	Gray	7 3/4" x 5" x 3"

Accepts a wide range of Intermatic time switches, including most T100, T170, T1900, T2000, C8800, EH, ET1100, ET1700, ET8000, ET90115, and ET90215 Series units



B.



Outdoor Steel Enclosures

Type 3R Rainproof Enclosures

- Drawn steel with gray or beige powder coat paint finish
- Combination 1/2" - 3/4" nominal knockouts with one on back and each side of enclosure, and two on bottom
- Separate grounding terminal
- Convenient mounting holes
- Lockable hasp holds door closed

Model #	Description	Color	H x W x D
B. 2T511GA*	For Time Switch Models That Snap into Enclosures	Gray	9 3/8" x 5 1/2" x 3 5/8"
C. 2T2485GA*	For Time Switch Models That Snap into Enclosures	Beige	9 3/8" x 5 1/2" x 3 5/8"
2T2331GA**	For Time Switch Models with Carryover	Gray	9 3/8" x 5 1/2" x 3 5/8"

**Available for T100, T170, T1900, T2000, C8800, EH, ET1100, ET1700, ET8000, ET90115, and ET90215 Series units*

***Available for T100CR, T170CR, T1400, and T1800 Series units*



C.



A.



Indoor Steel Enclosure

Type 1 Enclosure

- Drawn steel with gray powder coat paint finish
- Combination 1/2" and 3/4" nominal knockouts with one on back and each side of enclosure, and two on bottom
- Convenient mounting holes
- Lockable hasp holds door closed

Model #	Color	H x W x D
A. 2T2040GA	Gray	7 3/4" x 5" x 3"

Accepts a wide range of Intermatic time switches, including most T100, T170, T1900, T2000, C8800, EH, ET1100, ET1700, ET8000, ET90115, and ET90215 Series units



B.



Outdoor Steel Enclosures

Type 3R Rainproof Enclosures

- Drawn steel with gray or beige powder coat paint finish
- Combination 1/2" - 3/4" nominal knockouts with one on back and each side of enclosure, and two on bottom
- Separate grounding terminal
- Convenient mounting holes
- Lockable hasp holds door closed

Model #	Description	Color	H x W x D
B. 2T511GA*	For Time Switch Models That Snap into Enclosures	Gray	9 3/8" x 5 1/2" x 3 5/8"
C. 2T2485GA*	For Time Switch Models That Snap into Enclosures	Beige	9 3/8" x 5 1/2" x 3 5/8"
2T2331GA**	For Time Switch Models with Carryover	Gray	9 3/8" x 5 1/2" x 3 5/8"

*Available for T100, T170, T1900, T2000, C8800, EH, ET1100, ET1700, ET8000, ET90115, and ET90215 Series units

**Available for T100CR, T170CR, T1400, and T1800 Series units



C.