



## TG8 Recessed

UPC CODE	CATALOG NUMBER	DESCRIPTION	SERVICE SMART	SPEC SMART	STOCKED IN
734340607994	1TG232-01-UNV-1/2-EB	1x4, 2 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	✓		C,N,F
781370989132	2TG8217R-01-UNV-1/2-EB	2x2, 2 Lamp, 17W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast		✓	
781370943776	2TG8231U6R-01-UNV-1/2-EB	2x2, 2 Lamp, 31W U6 T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	✓		C,N,F
781370989149	2TG8317R-01-UNV-1/3-EB	2x2, 3 Lamp, 17W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast		✓	
734340981889	2TG8232-01-UNV-1/2-EB ●	2x4, 2 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	✓		C,N,F
734340976526	2TG8332-01-UNV-1/21-EB ●	2x4, 3 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	✓		C,N,F
734340976533	2TG8332-01-UNV-1/3-EB ●	2x4, 3 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	✓		C,N,F
734340981896	2TG8332-01-UNV-1/3-EB-LPT735 ●	2x4, 3 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast, w/ 735 Lamps	✓		C,N,F
781370017293	2TG8332-01-UNV-1/3-EB10I-LPT741 ●	2x4, 3 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast, w/ 741 Lamps	✓		C
734340976540	2TG8332-01-UNV-1/3-EB-F1-LPT735 ●	2x4, 3 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast, 6' Flex, w/ 735 Lamps	✓		C,F
782343338797	2TG8332-01-UNV-1/3-EB-F1-LPT741 ●	2x4, 3 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast, 6' Flex, w/ 741 Lamps	✓		C
734340996661	2TG8332-01-UNV-M11-1/42-EB	2x4, 3 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast, 11' Flex, Master Unit For Use w/ Satellite Unit		✓	
734340996678	2TG8332-01-000-S-X-1/42-EBIS	2x4, 3 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Satellite Unit For Use w/ Master Unit		✓	
734340976595	2TG8432-01-UNV-1/4-EB ●	2x4, 4 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	✓		C,N,F
734340996845	2TG8432-01-UNV-2/2-EB ●	2x4, 4 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	✓		C,N,F
734340981902	2TG8432-01-UNV-1/4-EB-LPT735 ●	2x4, 4 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast, w/ 735 Lamps	✓		C,N,F
734340981919	2TG8432-01-UNV-1/4-EB-LPT741 ●	2x4, 4 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast, w/ 741 Lamps	✓		C,N,F
734340976601	2TG8432-01-UNV-1/4-EB-F1-LPT735 ●	2x4, 4 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast, 6' Flex, w/ 735 Lamps	✓		C,F
734340976618	2TG8432-01-UNV-1/4-EB-F1-LPT741 ●	2x4, 4 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast, 6' Flex, w/ 741 Lamps	✓		C
782343040713	TG8FS01D	2x4 Pattern 12 Prismatic Acrylic Lens Replacement	✓		C,N,F
782343297872	TG8FS01DL-5PK	2x4 Pattern 12 Prismatic Acrylic Lens Replacement, 5 Pack	✓		C,N,F

## Recessed Accessories

UPC CODE	CATALOG NUMBER	DESCRIPTION	SERVICE SMART	SPEC SMART	STOCKED IN
734340775488	FMA14	1x4 Flange Mounting Frame Assembly For Recessed Fixtures	✓		C,N,F
734340775471	FMA22	2x2 Flange Mounting Frame Assembly For Recessed Fixtures	✓		C,N,F
734340775464	FMA24	2x4 Flange Mounting Frame Assembly For Recessed Fixtures	✓		C,N,F
782343501603	GCC	Grid Clip For Recessed Fixtures (4 each)	✓		F

\*C= Carrollton, Texas    F= Fontana, California    N= Norwich, Connecticut

“●” beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.



## TG8 Recessed

UPC CODE	CATALOG NUMBER	DESCRIPTION	SERVICE SMART	SPEC SMART	STOCKED IN
734340607994	1TG232-01-UNV-1/2-EB	1x4, 2 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	✓		C,N,F
781370989132	2TG8217R-01-UNV-1/2-EB	2x2, 2 Lamp, 17W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast		✓	
781370943776	2TG8231U6R-01-UNV-1/2-EB	2x2, 2 Lamp, 31W U6 T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	✓		C,N,F
781370989149	2TG8317R-01-UNV-1/3-EB	2x2, 3 Lamp, 17W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast		✓	
734340981889	<a href="#">2TG8232-01-UNV-1/2-EB</a> ●	2x4, 2 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	✓		C,N,F
734340976526	<a href="#">2TG8332-01-UNV-1/21-EB</a> ●	2x4, 3 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	✓		C,N,F
734340976533	<a href="#">2TG8332-01-UNV-1/3-EB</a> ●	2x4, 3 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	✓		C,N,F
734340981896	<a href="#">2TG8332-01-UNV-1/3-EB-LPT735</a> ●	2x4, 3 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast, w/ 735 Lamps	✓		C,N,F
781370017293	<a href="#">2TG8332-01-UNV-1/3-EB10I-LPT741</a> ●	2x4, 3 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast, w/ 741 Lamps	✓		C
734340976540	<a href="#">2TG8332-01-UNV-1/3-EB-F1-LPT735</a> ●	2x4, 3 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast, 6' Flex, w/ 735 Lamps	✓		C,F
782343338797	<a href="#">2TG8332-01-UNV-1/3-EB-F1-LPT741</a> ●	2x4, 3 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast, 6' Flex, w/ 741 Lamps	✓		C
734340996661	2TG8332-01-UNV-M11-1/42-EB	2x4, 3 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast, 11' Flex, Master Unit For Use w/ Satellite Unit		✓	
734340996678	2TG8332-01-000-S-X-1/42-EBIS	2x4, 3 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Satellite Unit For Use w/ Master Unit		✓	
734340976595	<a href="#">2TG8432-01-UNV-1/4-EB</a> ●	2x4, 4 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	✓		C,N,F
734340996845	<a href="#">2TG8432-01-UNV-2/2-EB</a> ●	2x4, 4 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	✓		C,N,F
734340981902	<a href="#">2TG8432-01-UNV-1/4-EB-LPT735</a> ●	2x4, 4 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast, w/ 735 Lamps	✓		C,N,F
734340981919	<a href="#">2TG8432-01-UNV-1/4-EB-LPT741</a> ●	2x4, 4 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast, w/ 741 Lamps	✓		C,N,F
734340976601	<a href="#">2TG8432-01-UNV-1/4-EB-F1-LPT735</a> ●	2x4, 4 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast, 6' Flex, w/ 735 Lamps	✓		C,F
734340976618	<a href="#">2TG8432-01-UNV-1/4-EB-F1-LPT741</a> ●	2x4, 4 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast, 6' Flex, w/ 741 Lamps	✓		C
782343040713	TG8FS01D	2x4 Pattern 12 Prismatic Acrylic Lens Replacement	✓		C,N,F
782343297872	TG8FS01DL-5PK	2x4 Pattern 12 Prismatic Acrylic Lens Replacement, 5 Pack	✓		C,N,F

## Recessed Accessories

UPC CODE	CATALOG NUMBER	DESCRIPTION	SERVICE SMART	SPEC SMART	STOCKED IN
734340775488	FMA14	1x4 Flange Mounting Frame Assembly For Recessed Fixtures	✓		C,N,F
734340775471	FMA22	2x2 Flange Mounting Frame Assembly For Recessed Fixtures	✓		C,N,F
734340775464	FMA24	2x4 Flange Mounting Frame Assembly For Recessed Fixtures	✓		C,N,F
782343501603	GCC	Grid Clip For Recessed Fixtures (4 each)	✓		F

\*C= Carrollton, Texas    F= Fontana, California    N= Norwich, Connecticut

“●” beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.