



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



30088J In-Sure Push-In Wire Conn, 88 6-PRT Blue, 100/Jar

Ideal

| | |
|------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | 30088J |
| Manufacturer | Ideal |
| Description | Push-In Wire Connector, Blue Insulation Color, +221 °F Operating Temperature, 0.607 In Overall Length, 0.603 In Overall Width, 0.729 In Overall Height, 600 V (Building Wire);1000 V (Maximum Signs/Lighting Fixture), 0.01 LB |
| Weight per unit | 1.2 (lbs/each) |
| Product Category | Electrical Fixture Conn (Nuts |

Features

| | |
|----------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| connection | 6 Stacked Ports |
| Voltage Rating | 600 V Maximum Building Wire, 1000 V Maximum Signs And Lighting Fixtures |
| Wire Size | #12 AWG - #20 AWG Solid, #14 AWG - #16 AWG (19 Strand Or Less) #18 AWG (7 Strand Or Less) Stranded, #12 AWG - #14 AWG (19 Strand Or Less) #16 AWG (26 Strand Or Less) 318 AWG (16 Strand Or Less) Stranded (Tin Bonded) |
| Wire Type | Solid, Stranded, Stranded (Tin Bonded) |

Material, Color, and Finish

| | |
|-------|------|
| Color | Blue |
|-------|------|

Dimensions and Weight

| | |
|------|----------------------------------------------------|
| Size | 0.607 IN Length X 0.603 IN Width X 0.729 IN Height |
|------|----------------------------------------------------|

Descriptions

| | |
|-------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | IN-SURE PUSH-IN WIRE CONN, 88 6-PRT BLUE, 100/JAR |
| Features | The In-Sure Push-In Wire Connector is perfect for residential, light commercial, lighting retrofit, and pre-fab wiring systems, or any other branch circuit wiring application where a traditional twist-on wire connector would be used. Simply push the wire in – the low insertion force makes it easy.The color-coded shell allows for quick identification of port configuration while the clear polycarbonate housing allows for visual verification of every connection. The ergonomic design is easier to grip which me |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Ideal |
| GTIN | 00783250460823 |
| UPC | 783250460823 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------|
| Category Description | WIRE NUTS |
| Type | Push-In |

Availability

| | |
|---------------------|----------|
| Manufacturer Status | Inactive |
| minimum qty | 100 |
| Status | Inactive |

Packaging

| | |
|-----------------|------|
| Carton | 100 |
| Package | 600 |
| Weight Per each | 1.18 |

Uses, Certifications, and Standards

| | |
|--------------------|------------------------------------------|
| standard | CSA C22.2 #188, 486C/467 UL Listed, RoHS |
| Temperature Rating | 105 DEG C Shell Rated |