



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



30430 9-1/2" Linesman Plier W/Ne, Crimp Die, Fish Tape

Ideal

| | |
|------------------|---|
| Catalog Number | 30430 |
| Manufacturer | Ideal |
| Description | Laseredge High-Leverage Side-Cutting Pliers With Crimping Die, Overall Length: 9-1/4 In, Vinyl-Coated, Comfort-Grip Handle, Drop-Forged, High-Carbon Steel, Side Cutter Plier, New England Nose, Cutting Edge: Serrated, For Cutting Hardened Wire, Bolts and Acsr, Crimps Bare and Insulated Terminals |
| Weight per unit | 1.2 (lbs/each) |
| Product Category | Pliers, Wrenches, Saw, Pouches |

Features

| | |
|-------------|--------------------------------|
| Handle Type | Vinyl-Coated, Comfort-Grip |
| Material | Drop-Forged, High-Carbon Steel |
| plier type | Side Cutter |

Dimensions and Weight

| | |
|----------------|-------|
| Overall Length | 9-1/4 |
|----------------|-------|

Descriptions

| | |
|------------------|--|
| Description | 9-1/2" LINESMAN PLIER W/NE, CRIMP DIE, FISH TAPE |
| Features | The IDEAL® Made in the U.S.A. tool line uses forged-steel construction, which provides extra strength and hardness without sacrificing flexibility. Features knife-to-knife cutting blades, high leverage pivots, cam-action fish tape puller and dual crimp dies. Knife-to-knife blades rarely need sharpening Cuts hardened wire, bolts and stainless steel wire |
| Long Description | LASERedge High-Leverage Side-Cutting Pliers With Crimping Die, Overall Length: 9-1/4 IN, Vinyl-Coated, Comfort-Grip Handle, Drop-Forged, High-Carbon Steel, Side Cutter Plier, New England Nose, Cutting Edge: Serrated, For Cutting Hardened Wire, Bolts And ACSR, Crimps Bare And Insulated Terminals |
| Product Type | Side Cutter W Crimp 9 In |
| Special Features | Drop-forged, high-carbon steel construction withstands toughest applications; Knife-to-anvil blades never need sharpening; Laser-hardened blades and serrated jaws for long-term durability; High-leverage design provides 40 PCT more cutting power; Unique reverse rivet protects smooth action of plier movement; Crimps bare and insulated terminals; Vinyl-coated, comfort-grip handles; Lifetime guarantee |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250304301 |
| Manufacturers Part Number | 30430 |
| sub brand | LASERedge |
| UPC | 783250304301 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | HAND TOOLS |
| Type | High-Leverage Side-Cutting Pliers With Crimping Die |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 1.18 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | For Cutting Hardened Wire, Bolts And ACSR, Crimps Bare And Insulated Terminals |
|-------------|--|