

## No. 7 Corrosive chemical pipe thread sealant

| Code  | Description | Qty. |
|-------|-------------|------|
| 17432 | 1 pt.       | 4    |

- FEATURES**
- Soft Set
  - Lead free

**Application** • Slow drying sealant for use with lines carrying corrosive chemicals: diluted acids, caustics and other chemical solutions



- Recommended for**
- Galvanized Steel
  - Iron
  - Brass
  - Copper
  - Aluminum
  - Stainless Steel



## No. 21 Black, slow dry/soft set pipe thread sealant

| Code  | Description | Qty. |
|-------|-------------|------|
| 28651 | ½ pt.       | 24   |
| 28541 | 1 pt.       | 12   |
| 28371 | 1 gal.      | 4    |
| 28111 | 5 gal.      | 1    |
| 28222 | 55 gal.     | 1    |



- FEATURES**
- Black sealant
  - Lead free
  - Multi-purpose



**Application** • Soft set sealant for lines carrying a wide range of liquids and gases • For applications where black color is preferred

- Brushable from 20°F to 140°F

- Recommended for**
- Galvanized Steel
  - Iron
  - Brass
  - Copper
  - Aluminum
  - Stainless Steel
  - Polyethylene
  - RTRP
  - PVC

Also available in 55 gal. container.

## PTFE Tape 100% pure PTFE pipe thread sealant tape

| Code  | Description | Qty. |
|-------|-------------|------|
| 35942 | ½" x 260"   | 12   |
| 35943 | ½" x 520"   | 12   |
| 35944 | ½" x 1296"  | 12   |
| 35945 | ¾" x 260"   | 12   |
| 35946 | ¾" x 520"   | 12   |
| 35947 | ¾" x 1296"  | 12   |
| 35948 | 1" x 260"   | 12   |
| 35949 | 1" x 520"   | 12   |



**Application** • Resistant to most liquids and gases as it is completely inert

- Available in a wide variety of sizes.



## No. 7 Corrosive chemical pipe thread sealant

| Code  | Description | Qty. |
|-------|-------------|------|
| 17432 | 1 pt.       | 4    |

**FEATURES**

- Soft Set
- Lead free

**Application** • Slow drying sealant for use with lines carrying corrosive chemicals: diluted acids, caustics and other chemical solutions



- Recommended for**
- Galvanized Steel
  - Iron
  - Brass
  - Copper
  - Aluminum
  - Stainless Steel



## No. 21 Black, slow dry/soft set pipe thread sealant

| Code  | Description | Qty. |
|-------|-------------|------|
| 28651 | ½ pt.       | 24   |
| 28541 | 1 pt.       | 12   |
| 28371 | 1 gal.      | 4    |
| 28111 | 5 gal.      | 1    |
| 28222 | 55 gal.     | 1    |



**FEATURES**

- Black sealant
- Lead free
- Multi-purpose



**Application** • Soft set sealant for lines carrying a wide range of liquids and gases • For applications where black color is preferred • Brushable from 20°F to 140°F

- Recommended for**
- Galvanized Steel
  - Iron
  - Brass
  - Copper
  - Aluminum
  - Stainless Steel
  - Polyethylene
  - RTRP
  - PVC

Also available in 55 gal. container.

## PTFE Tape 100% pure PTFE pipe thread sealant tape

| Code  | Description | Qty. |
|-------|-------------|------|
| 35942 | ½" x 260"   | 12   |
| 35943 | ½" x 520"   | 12   |
| 35944 | ½" x 1296"  | 12   |
| 35945 | ¾" x 260"   | 12   |
| 35946 | ¾" x 520"   | 12   |
| 35947 | ¾" x 1296"  | 12   |
| 35948 | 1" x 260"   | 12   |
| 35949 | 1" x 520"   | 12   |

**Application** • Resistant to most liquids and gases as it is completely inert

- Available in a wide variety of sizes.

