



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 35164 RD Shank Screwdr, 1/4 X 4"

*Ideal*

|                  |  |
|------------------|--|
| Catalog Number   | 35164  |
| Manufacturer     | Ideal  |
| Description      | Ideal, Screwdriver, Heavy-Duty, Slotted, Keystone Tip, Tip Size: 1/4 In, Overall Length: 8-3/8 In, Shank Length: 4 In, Shank Shape: Round, Handle Type: Cushioned Rubber Grip, Blade Material: Chrome Vanadium Steel, Tip Type: Keystone, Shank Size: 1/4 In, Warranty: Lifetime Guarantee |
| Weight per unit  | 0.2833 (lbs/each)  |
| Product Category | Pliers, Wrenches, Saw, Pouches   |

### Features

|              |                       |
|--------------|-----------------------|
| Handle Type  | Cushioned Rubber Grip |
| Shank Length | 4                     |
| Shank Shape  | Round                 |
| Tip Size     | 1/4                   |
| tip type     | Keystone              |

### Material, Color, and Finish

|                |                       |
|----------------|-----------------------|
| Blade Material | Chrome Vanadium Steel |
|----------------|-----------------------|

### Dimensions and Weight

|                |       |
|----------------|-------|
| Overall Length | 8-3/8 |
|----------------|-------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | RD SHANK SCREWDR, 1/4 X 4"  |
| extra long description | IDEAL 35-164 RD SHANK SCREWDR, 1 4X   |
| Features               | The Heavy-Duty Round Shaft Keystone Cushioned-Grip Screwdriver has a cushion-grip handle that is resistant to oil, gas and water, and helps to prevent slippage for greater torque and superior comfort. They feature nickel chrome plated vanadium steel heavy-duty square shanks and offer wrench-assisted turning. It has a cross-ground black oxide finish tip to provide a precise and secure fit in the screw slot. The handle ends are all color-coded for quick and easy identification. Screwdriver meets ASTM F1505-0 |
| Long Description       | IDEAL, Screwdriver, Heavy-Duty, Slotted, Keystone Tip, Tip Size: 1/4 IN, Overall Length: 8-3/8 IN, Shank Length: 4 IN, Shank Shape: Round, Handle Type: Cushioned Rubber Grip, Blade Material: Chrome Vanadium Steel, Tip Type: Keystone, Shank Size: 1/4 IN, Warranty: Lifetime Guarantee  |
| Product Type           | RD Shank Screwdr, 1 4X4 In  |
| Special Features       | Features: Larger Shank For Heavy-Duty Applications; Identification Mark On Ends; Vapor-Blasted Tip Prevents Plate Chipping; Precision Ground Tip Provides Secure Fit In Screw Slot; Square-Shank Models Offer Wrench-Assisted Turning; Tough, Chrome Vanadium Steel Shank; Cushioned Rubber Grips; Shank Size: 1/4 IN; Warranty: Lifetime Guarantee   |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Ideal          |
| GTIN                      | 00783250351640 |
| Manufacturers Part Number | 35-164         |
| UPC                       | 783250351640   |

## Taxonomies, Classifications, and Categories

|                      |                                   |
|----------------------|-----------------------------------|
| Category Description | HAND TOOLS                        |
| Type                 | Heavy-Duty, Slotted, Keystone Tip |

## Packaging

|                 |        |
|-----------------|--------|
| Carton          | 1      |
| Weight Per each | 0.2833 |