



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **3630124XS Encl 36X30X12 N4X SS 1DR CH Clamp CVR** *Cooper B-Line/Cable Tray*

Catalog Number	3630124XS
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 36" Height, 12" Length, 30" Width, Nema 4X, Hinged Cover, 4XS Enclosure, Wall Mount, Medium Single Door, External Mounting Feet, 304 Stainless Steel, Seamless Poured In-Place Gasket
Weight per unit	90.5 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

### Features

dimensions	12.0000 IN X 30.0000 IN X 36.0000 IN
Material	304 Stainless Steel
Mounting Type	Wall

### Material, Color, and Finish

Color	Gray
-------	------

### Dimensions and Weight

Size	30.00 In Width X 12.00 In Depth X 36.00 In Height
------	---

### Descriptions

Description	ENCL 36X30X12 N4X SS 1DR CH CLAMP CVR
extra long description	B-LINE 363012-4XS TYPE 4X SSL SGL-D
Features	Eaton's B-Line series wall mounted panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments.
Long Description	Eaton B-Line series wall mounted panel enclosure, 36" height, 12" length, 30" width, NEMA 4X, Hinged cover, 4XS enclosure, Wall mount, Medium single door, External mounting feet, 304 stainless steel, Seamless poured in-place gasket
Product Type	Type 4X SSL SGL-Door Enc, 36X30X12
Special Features	Stainless door clamps

### Manufacturer Information

Brand	Eaton
GTIN	00782051870428
Manufacturers Part Number	363012-4XS
UPC	782051870428

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Wall mounted panel enclosure



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	90.498

## Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative Energy Datacenters - IT Space: CI and Hyper Converged Commercial / Institutional Buildings / Structures - Power Distribution and Controls Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other Other IT and Datacom - IT and Datacomm - Other Commercial / Institutional Buildings / Structures - Safety and Security Systems Utility - Substations, Utility Transmission and Distribution Commercial / Institutional Buildings /
Mounting	WALL
nema rating	4X
standard	NEMA, CSA C22.2., UL 50