



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 36305 Tko Carbide-Tipped Hole Cutter, 1-3/8"

*Ideal*

Catalog Number	36305
Manufacturer	Ideal
Description	Tko Carbide Tipped Hole Cutter, 1-3/8 In Hole, For 1 In Conduit Pipe
Weight per unit	0.4500 (lbs/each)
Product Category	Bits, Parts, Accessories

### Features

Hole Size	1-3/8
-----------	-------

### Descriptions

Description	TKO CARBIDE-TIPPED HOLE CUTTER, 1-3/8"
extra long description	IDEAL 36-305 1-3 8" CARBIDE HOLE CU
Features	TKO Hole Cutters offer the most efficient and cleancutter replacement for traditional knockouts, by makingsmooth holes in a fraction of the time at a fraction of thecost. Specifically designed to cut sheet metal, TKO cutterswill even cut stainless steel with fine grained, carbidetips. The innovative design includes the exclusiveSmoothStart replaceable pilot drill, which guides thecutter to the surface, avoiding cutter damage andproviding smoother holes. An integral overdrill flangeprevents cutter penetrati
Long Description	TKO Carbide Tipped Hole Cutter, 1-3/8 IN Hole, For 1 IN Conduit Pipe
Product Type	1-3 8" Carbide Hole Cutter
Special Features	SmoothStart pilot drill prevents carbide damage by gradually guiding cutter to material; Precision-ground carbide teeth for fast cutting of clean, round holes; Designed specifically for sheet metal cutting, even stainless-steel; Over drill flange built-in to prevent penetration beyond the sheet metal

### Manufacturer Information

Brand	Ideal
GTIN	00783250670604
Manufacturers Part Number	36-305
UPC	783250670604

### Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	Carbide Tipped Hole Cutter



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.45

## Uses, Certifications, and Standards

Application	For 1 IN Conduit Pipe
-------------	-----------------------