



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



391 5" Malleable Insulated Grounding Bushing *Bridgeport Fittings*

| | |
|------------------|--|
| Catalog Number | 391 |
| Manufacturer | Bridgeport Fittings |
| Description | Bushing, Insulated, Grounding, Malleable Iron, Size 5 Inch |
| Weight per unit | 1.5 (lbs/each) |
| Product Category | Rigid Conduit Fittings - Steel |

Features

| | |
|----------|----------------|
| Material | Malleable Iron |
| media | Yes |

Material, Color, and Finish

| | |
|--------|---------------------------|
| Color | Grey with Black Insulator |
| Finish | Zinc Electroplated |

Dimensions and Weight

| | |
|------|---|
| Size | 5 |
|------|---|

Descriptions

| | |
|------------------------|--|
| Description | 5" MALLEABLE INSULATED GROUNDING BUSHING |
| extra long description | BPT 391 5" GRND. BUSH. INS. |
| Long Description | Bushing, Insulated, Grounding, Malleable Iron, Size 5 Inch |
| Product Type | 5" GRND. Bush. Ins. |
| Special Features | Grounding Lug Wire Capacity #6 - #250 MCM |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Bridgeport |
| GTIN | 00781747003911 |
| UPC | 781747003911 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods |
| Type | BUSHING |

Trade Size

| | |
|------------|---|
| Trade Size | 5 |
|------------|---|

Packaging

| | |
|-----------------|------|
| Carton | 5 |
| Weight Per each | 1.48 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Used with locknut to terminate service conduit to cabinet. Lug provided for bonding jumper to neutral busbar. Grounding lug: aluminum alloy 6061-T6. Plastic metaliner prevents damage to wire insulation. 1/2" thru 4" rated 150 degree C, 5" and 6" rated 105 degree C.

standard

cULus

Temperature Rating

150°C