






## 403214-TC3R-SP1



Catalog Number	403214-TC3R-SP1	Latch	Pad Locking Draw Latch Installed
Marketing Product Description	40x14X32 Hinge Cover Type 3R UL Listed Steel No Knockouts ANSI 61 Gray Padlocking Draw Latch Back Panel Installed Continuous Hinge Special Stud Mounting Emboss Holes In Back	Hinge	Continuous Hinge
UPC	784572517684	NEMA Rating	Type 3R
Length (IN)	14	Depth	14
Width (IN)	32	Finish	Painted
Height (IN)	40		
Weight (LB)	158		
Brand Name	Milbank		
Type	Telephone Cabinet		
Special Features	Steel Back Panel Installed		
Application	Outdoor Telephone Cabinet		
Standard	UL Listed		
Number Of Outlet	0		
Door	Single Door		
Material	Steel with Powder Coat Finish		
Cable Entry	No Knockouts		
Size	14L x 40W x 32H		
Color	ANSI 61 Gray		
Mounting	Wall Mount		

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.



All dimensions are +/- 1/16".  
Drawing views are not to scale.

Version:

1

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility, and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.






# 403214-TC3R-SP1



Catalog Number	403214-TC3R-SP1	Latch	Pad Locking Draw Latch Installed
Marketing Product Description	40x14X32 Hinge Cover Type 3R UL Listed Steel No Knockouts ANSI 61 Gray Padlocking Draw Latch Back Panel Installed Continuous Hinge Special Stud Mounting Emboss Holes In Back	Hinge	Continuous Hinge
UPC	784572517684	NEMA Rating	Type 3R
Length (IN)	14	Depth	14
Width (IN)	32	Finish	Painted
Height (IN)	40		
Weight (LB)	158		
Brand Name	Milbank		
Type	Telephone Cabinet		
Special Features	Steel Back Panel Installed		
Application	Outdoor Telephone Cabinet		
Standard	UL Listed		
Number Of Outlet	0		
Door	Single Door		
Material	Steel with Powder Coat Finish		
Cable Entry	No Knockouts		
Size	14L x 40W x 32H		
Color	ANSI 61 Gray		
Mounting	Wall Mount		

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.



**All dimensions are +/- 1/16".  
Drawing views are not to scale.**

Version 1

1

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility, and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.