



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

120/208 VOLTS 120/208 VOLTS
120/208 VOLTS 120/208 VOLTS

44296 Voltage & Conduit Marker, "120/280", Med, 4/Card

Ideal

| | |
|------------------|---|
| Catalog Number | 44296 |
| Manufacturer | Ideal |
| Description | Ideal, Marker Card, Voltage and Conduit, Medium, Size: 1-1/8 In Width, Length: 4-1/2 In, Material: Vinyl-Impregnated Cloth, Legend: 120/208V, Temperature Range: -40 to 180 Deg F, Text Size: 3/4 In, Adhesion: 45 Oz/In Width Ultimate |
| Weight per unit | 0.0200 (lbs/each) |
| Product Category | Markers & Marking Tapes |

Features

| | |
|-------------------|-------------------------|
| Legend | 120/208V |
| Material | Vinyl-Impregnated Cloth |
| Number of Markers | 20 |

Dimensions and Weight

| | |
|--------|-------|
| Length | 4.5 |
| Width | 1-1/8 |

Descriptions

| | |
|------------------------|---|
| Description | VOLTAGE & CONDUIT MARKER, "120/280", MED, 4/CARD |
| extra long description | IDEAL 44-296 WIRE MRKR,120 208V,TYP |
| Features | Identify junction boxes, switches, circuit breakers, raceways, pipe and fuse boxesNon-conductive for user safetyHigh-adhesion properties with easy removabilityVinyl-impregnated cloth construction for long-lasting durabilityResist abrasion, moisture, dirt and oilNon-smear, black legend on bright orange background for high visibilityTemperature Range: -40°F to 180°F (-40°C to 82°C)Adhesion: 45 oz./in. width ultimate SELECT PART N |
| Long Description | IDEAL, Marker Card, Voltage And Conduit, Medium, Size: 1-1/8 IN Width, Length: 4-1/2 IN, Material: Vinyl-Impregnated Cloth, Legend: 120/208V, Temperature Range: -40 to 180 DEG F, Text Size: 3/4 IN, Adhesion: 45 OZ/IN Width Ultimate |
| Product Type | Voltage & Conduit Marker, "120/280", Med, 4/Card |
| Special Features | Adhesion: 45 OZ/IN Width Ultimate;Features: Identify Junction Boxes, Switches, Circuit Breakers,Raceways, Pipe And Fuse Boxes;High-Adhesion Properties With Easy Removability;Non-Conductive For User Safety;Non-Smear, Black Legend On Bright Orange BackgroundFor High Visibility;Resist Abrasion, Moisture, Dirt And Oil;Temperature Range: -40 DEGF To 180 DEGF (-40 DEGC To 82 DEGC) Adhesion: 45 Oz/IN Width Ultimate;Temperature Range: -40 to 180 DEG F;Text Size: 3/4 IN;Vinyl-Impregnated Cloth Construction Provides |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250442966 |
| Manufacturers Part Number | 44-296 |
| UPC | 783250442966 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------|
| Category Description | WIRE LUBE, MARKERS, & TIES |
| Type | Voltage And Conduit, Medium |

Packaging

| | |
|-----------------|------|
| Carton | 25 |
| Weight Per each | 0.02 |

Uses, Certifications, and Standards

| | |
|----------|------|
| standard | RoHS |
|----------|------|