



Catalog Number: 4436-GSC3R-NK
Item Description: N3R SCREW CVR GUTTER NK
UPC Code: 784572106499


Brand Name: Milbank
Type: Wiring Trough
Special Features: Key Locking Cylinder Latch Provision,
Sealing Eye Lance
Application: Wireway
Standard: UL Listed, Type 3R
Cover Type: Screw Cover
Enclosure: Outdoor Enclosure
Nominal Cross Section: 4x4
Straight Section Length: 36
Material: Steel with Powder Coat Finish
Finish: ANSI 61 Gray
Knockouts: False





Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

| CAT. NO. | U/L LABEL |
|---------------|-----------|
| 4436-GSC3R | 1002943 |
| RC-4436-GSC3R | 1125051 |
| SPRSCG-4436 | 1132575 |

| ITEM | QTY. | PART NUMBER | DESCRIPTION |
|------|------|-------------|-------------------------|
| 1 | 1 | 1153003 | BACK WELDMENT |
| 2 | 1 | 1004405 | FRONT |
| 3 | 3 | 1001290 | SCREW, 10-32 X 5/16 |
| 4 | 1 | 1002898 | LABEL, RATING 4x4 GSC3R |
| 5 | 1 | (SEE CHART) | UL LABEL, WIREWAY |
| 6 | 1 | 1003085 | PAD (NOT SHOWN) |



| | | | |
|--|---------|---|--------------|
| Material: 16 GA. GALV. STEEL | |  General Offices: Kansas City, MO | |
| Shear/ Die#: | | | |
| Finish: MILBANK LIGHT GRAY | | Title: SCREW COVER WIREWAY NEMA TYPE 3R | |
| Part Wt.: | | Catalog No.: (SEE CHART) | |
| Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X* ±2* | | Customer: | |
| Third Angle  | | Drawing No.: 270 | |
| REV. | DATE | DESCRIPTION | BY |
| B | 5/6/11 | REDRAW INTO SOLIDWORKS; UPDATE K.O. PATTERN; 1004405 WAS 1010725 (ECO #20576) | D.F. |
| C | 8/12/11 | ADD #1003085 PAD WITH SLIT (mECO#21106) | JLT |
| Scale: NTS | | Checked By: | Date: 5/6/11 |
| Drawn By: D.F. | | Approved By: | Sheet 1 of 1 |



Catalog Number: 4436-GSC3R-NK
Item Description: N3R SCREW CVR GUTTER NK
UPC Code: 784572106499


Brand Name: Milbank
Type: Wiring Trough
Special Features: Key Locking Cylinder Latch Provision,
Sealing Eye Lance
Application: Wireway
Standard: UL Listed, Type 3R
Cover Type: Screw Cover
Enclosure: Outdoor Enclosure
Nominal Cross Section: 4x4
Straight Section Length: 36
Material: Steel with Powder Coat Finish
Finish: ANSI 61 Gray
Knockouts: False





Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

| CAT. NO. | U/L LABEL |
|---------------|-----------|
| 4436-GSC3R | 1002943 |
| RC-4436-GSC3R | 1125051 |
| SPRSCG-4436 | 1132575 |

| ITEM | QTY. | PART NUMBER | DESCRIPTION |
|------|------|-------------|-------------------------|
| 1 | 1 | 1153003 | BACK WELDMENT |
| 2 | 1 | 1004405 | FRONT |
| 3 | 3 | 1001290 | SCREW, 10-32 X 5/16 |
| 4 | 1 | 1002898 | LABEL, RATING 4x4 GSC3R |
| 5 | 1 | (SEE CHART) | UL LABEL, WIREWAY |
| 6 | 1 | 1003085 | PAD (NOT SHOWN) |



| | | | |
|--|---------|---|--------------|
| Material: 16 GA. GALV. STEEL | |  General Offices: Kansas City, MO | |
| Shear/ Die#: | | | |
| Finish: MILBANK LIGHT GRAY | | Title: SCREW COVER WIREWAY NEMA TYPE 3R | |
| Part Wt.: | | Catalog No.: (SEE CHART) | |
| Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X* ±2* | | Customer: | |
| Third Angle  | | Drawing No.: 270 | |
| REV. | DATE | DESCRIPTION | BY |
| B | 5/6/11 | REDRAW INTO SOLIDWORKS; UPDATE K.O. PATTERN; 1004405 WAS 1010725 (ECO #20576) | D.F. |
| C | 8/12/11 | ADD #1003085 PAD WITH SLIT (mECO#21106) | JLT |
| Scale: NTS | | Checked By: | Date: 5/6/11 |
| Drawn By: D.F. | | Approved By: | Sheet 1 of 1 |