



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



44819 Plug Lockout, 220/250V, 3-1/4 X 3-1/4 X 7"

Ideal

Catalog Number	44819
Manufacturer	Ideal
Description	Ideal, Plug Lockout, Material: Durable Plastic Body, Voltage Rating: 220/550 V, Length: 7 In, Width: 3-1/4 In, Capacity: Up to 3/8 In Shackles
Weight per unit	0.7600 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

Material	Durable Plastic Body
Voltage Rating	220/550

Dimensions and Weight

Length	7
Width	3-1/4

Descriptions

Description	PLUG LOCKOUT, 220/250V, 3-1/4 X 3-1/4 X 7"
extra long description	IDEAL 44-819 Plug Lockout,Ideal,Dur
Features	IDEAL Plug Lockouts feature durable plastic bodies that resist wear, chemical, and job-site abuse. They can accommodate cable ties or padlocks (with up to 3/8-in. shackles). Plug Lockouts also accommodate a variety of electrical plug and cord sizes to avoid accidental connection or disconnection. Lockout is RoHS compliant.
Long Description	IDEAL, Plug Lockout, Material: Durable Plastic Body, Voltage Rating: 220/550 V, Length: 7 IN, Width: 3-1/4 IN, Capacity: Up To 3/8 IN Shackles
Product Type	Plug Lockout, Ideal, Durable Plastic Bdy, 220/550 V, 7.000 In Le
Special Features	Features: Accommodate A Variety Of Electrical Plug And Cord Sizes To Prevent Accidental Connection Or Disconnection; Durable Plastic Body Resists Wear, Chemicals And Abuse; Accommodates Cable Ties Or Padlocks With Up To 3/8 IN Shackles; Capacity: Up To 3/8 IN Shackles

Manufacturer Information

Brand	Ideal
GTIN	00783250448197
Manufacturers Part Number	44-819
UPC	783250448197

Taxonomies, Classifications, and Categories

Category Description	SAFETY PRODUCTS
----------------------	-----------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 1

Weight Per each 0.76

Uses, Certifications, and Standards

standard RoHS