



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 48111828 M18 Redlithium XC Extended Capacity Battery

*Milwaukee Electric Tool*

Catalog Number	48111828
Manufacturer	Milwaukee Electric Tool
Description	Delivers More Runtime, Power and Speed Than Standard Lithium-Ion Batteries. The M18™ Redlithium™ XC Extended Capacity Battery Is Designed With Superior Pack Construction, Electronics, and Performance to Optimize Work Per Charge and Work Over Pack Life. It Offers 3.0 Amp-Hours Of Runtime. With Built-In Milwaukee Durability, This Battery Runs Cooler and Performs In Climates Below 0°F/-18°C. Managed By Milwaukee'S Exclusive Redlink™ Intelligence, The Battery Features Overload Protection to Prevent You From Da
Weight per unit	1.6 (lbs/each)
Product Category	Batteries & Chargers

### Features

Battery Voltage	18
charge time	1.0
nominal voltage	18

### Material, Color, and Finish

Housing Material	Plastic/Rubber
------------------	----------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	M18 REDLITHIUM XC EXTENDED CAPACITY BATTERY
extra long description	MILW 48-11-1828 M18™ 3.0Ah Battery
Features	Milwaukee Tool is committed to protecting our users's investments by providing high performing, trade-focused solutions that are fully compatible with M18™ REDLITHIUM™ batteries. The M18™ system has over 200 performance-driven solutions, and growing!
Long Description	Delivers more runtime, power and speed than standard lithium-ion batteries. The M18™ REDLITHIUM™ XC extended capacity battery is designed with superior pack construction, electronics, and performance to optimize work per charge and work over pack life. It offers 3.0 amp-hours of runtime. With built-in Milwaukee durability, this battery runs cooler and performs in climates below 0°F/-18°C. Managed by Milwaukee's exclusive REDLINK™ Intelligence, the battery features overload protection to prevent you from da
Product Type	M18™ 3.0AH Battery Pack
Special Features	3.0 AMP Hour - 54 WTT Hour Battery; High Current Discharge - Increased Power And Performance; Equivalent Run-Time With 40 PCT Less Weight Than An 18V NiCd Battery; Lithium-Ion Battery Delivers Long Life And Run Time With Fade-Free Power; Battery Fuel Gauge - Displays Remaining Run-Time; Overload Protection - Prevents User From Damaging Their Cordless Power Tool Investment In Abusive Situations; Temperature Management System - Keeps Battery In Ideal Temperature Range To Provide Maximum Life; Individual Cell

## Manufacturer Information

Brand	Milwaukee®
GTIN	00045242155385
Manufacturers Part Number	48-11-1828
UPC	045242155385

## Taxonomies, Classifications, and Categories

Category Description	FLASHLIGHTS AND BATTERIES
Type	XC High Capacity

## Packaging

Carton	1
Package	16
Weight Per each	1.6

## Uses, Certifications, and Standards

Application	For Milwaukee M18 Cordless Tools
-------------	----------------------------------