



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 470SA 1-1/4" Alu FM7 CVR Assy

Appleton/Oz Gedney

Catalog Number	470SA
Manufacturer	Appleton/Oz Gedney
Description	FM7 Wedge-Lok Blank Clip Cover With Screw, Hub Size: 1-1/4 In, Form: 7, Mounting: Screw-In, Material: Stamped Aluminum, Finish: Natural Aluminum, Standard: UI 514A, UI 514B, UI File Number E2527, Csa C22.2 No. 18.3, Csa 065183, Nema FB-1, F
Weight per unit	0.4000 (lbs/each)
Product Category	Alum

### Features

Form	7
------	---

### Material, Color, and Finish

Finish	Natural Aluminum
--------	------------------

### Dimensions and Weight

Hub Size	1-1/4
----------	-------

### Descriptions

Description	1-1/4" ALU FM7 CVR ASSY
extra long description	APP 470SA 1 1/4 FM7 COVER STAMPED
Long Description	FM7 Wedge-Lok Blank Clip Cover With Screw, Hub Size: 1-1/4 IN, Form: 7, Mounting: Screw-In, Material: Stamped Aluminum, Finish: Natural Aluminum, Standard: UL 514A, UL 514B, UL File Number E2527, CSA C22.2 No. 18.3, CSA 065183, NEMA FB-1, F
Product Type	1 1/4 FM7 Cover Stamped-Alum
Special Features	Approved for use in wet locations;Stainless steel screws;The cover is secured with clips, not screws;Unique Wedge-Lok clip cover design allows easy removal without damaging the conduit body;Wiring capacity: 2 CU-IN as per NEC 314.16(A)

### Manufacturer Information

Brand	Appleton
GTIN	00781381601191
Manufacturers Part Number	470SA
UPC	781381601191

### Taxonomies, Classifications, and Categories

Category Description	FORM 7, 8, CONDULETS, COVERS, & GASKETS
Type	Blank Clip Cover With Screw



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	20
Package	100
Weight Per each	0.4

## Uses, Certifications, and Standards

Application	For FM7 Unilet Conduit Outlet Bodies
Mounting	Screw-In
standard	UL 514A, UL 514B, UL File Number E2527, CSA C22.2 No. 18.3, CSA 065183, NEMA FB-1