



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



48270621 Flat Boring Bit 5/8" X 6"

Milwaukee Electric Tool

| | |
|------------------|---|
| Catalog Number | 48270621 |
| Manufacturer | Milwaukee Electric Tool |
| Description | Bore Small, Clean Holes At Any Angle In A Variety Of Materials With The Economical Milwaukee® 5/8 In. X 6 In. Flat Boring Bit. This Premium Quality Flat Boring Bit Is Made Of Heat-Treated High Carbon Steel, So The Drill Point and Cutting Edge Can Be Resharpener For Cost Savings and Long Life. Bore Clean, Fast Holes At Any Angle In Wood, Plastic, Plywood and Formica. This Bit Offers A 6 In. Drilling Depth But Can Be Used With A 12 In. Extension (48-28-3350) For Extended Deep-Hole Drilling. 3/16 In. Shank Di |
| Weight per unit | 0.1130 (lbs/each) |
| Product Category | Bits, Parts, Accessories |

Features

| | |
|----------------|--------------------------------|
| Flute Length | 5 |
| Material | Heat-Treated High-Carbon Steel |
| Shank Diameter | 0.25 |

Dimensions and Weight

| | |
|----------------|-------|
| Length | 6 |
| Overall Length | 6-1/8 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | FLAT BORING BIT 5/8" X 6" |
| extra long description | MILW 48-27-0621 Flat Boring Bit 5/8 |
| Features | MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening, |
| Long Description | Bore small, clean holes at any angle in a variety of materials with the economical Milwaukee® 5/8 in. x 6 in. flat boring bit. This premium quality flat boring bit is made of heat-treated high carbon steel, so the drill point and cutting edge can be resharpened for cost savings and long life. Bore clean, fast holes at any angle in wood, plastic, plywood and Formica. This bit offers a 6 in. drilling depth but can be used with a 12 in. extension (48-28-3350) for extended deep-hole drilling. 3/16 in. shank di |
| Product Type | Flat Boring Bit 5/8 In. X 6 In. |
| Short Description | Flat Boring Bt 5/8inx6in |
| Special Features | 5/8 IN Bit Diameter; 1/4 IN Shank Diameter; 6-1/8 IN Overall Length; Drill Point And Cutting Edges Can Be Resharpened |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Milwaukee® |
| GTIN | 00045242120857 |
| Manufacturers Part Number | 48-27-0621 |
| UPC | 045242120857 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------|
| Category Description | BITS, BLADES, AND HOLE SAWS |
| Type | STUBBY |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 6 |
| Weight Per each | 0.113 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | For Bores Clean Holes At Any Angle In Wood, Plastic, Plywood And Formica |
|-------------|--|