



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



48430620 12" 24 Tpi Hack Saw Blade

Milwaukee Electric Tool

Catalog Number	48430620
Manufacturer	Milwaukee Electric Tool
Description	Greenlee 10038 Greenlee 3331224 Greenlee 333-1224 Ideal 35263 Ideal 35-263 Ideal 35272 Ideal 35-272 Klein 1224BIP Klein 1224BI-P Lenox 20155 Lenox S224HE Milwaukee 48430620 Milwaukee 48-43-0620 Morris 13014 Morse HHB122024T10 Morse HHB1224T10 Morse HHC12242 Morse HHC1224-2 Starrett KBS1224-10 Starrett KBS1224-2
Weight per unit	0.4300 (lbs/each)
Product Category	Hand Tool Bits, Parts, Acessor

Features

Teeth per Inch	24
----------------	----

Dimensions and Weight

Length	12
Thickness	025
Width	0.5

Descriptions

Description	12" 24 TPI HACK SAW BLADE
Long Description	Greenlee 10038 Greenlee 3331224 Greenlee 333-1224 IDEAL 35263 IDEAL 35-263 IDEAL 35272 IDEAL 35-272 Klein 1224BIP Klein 1224BI-P Lenox 20155 Lenox S224HE Milwaukee 48430620 Milwaukee 48-43-0620 Morris 13014 Morse HHB122024T10 Morse HHB1224T10 Morse HHC12242 Morse HHC1224-2 Starrett KBS1224-10 Starrett KBS1224-2
Product Type	12" 24 Tpi Hack Saw Blade
Special Features	Bi-Metal For Greater Durability; For Cutting Common Materials 1/8 IN - 3/8 IN Thick; Fits Most 12 IN Hack Saw Frames; Package Quantity: 10

Manufacturer Information

Brand	Milwaukee Electric Tool
GTIN	00045242139859
Manufacturers Part Number	48-43-0620
sub brand	MILWAUKEE
UPC	045242139859

Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	Hack Saw



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Manufacturer Status Inactive

Status Inactive

Packaging

Carton 1

Weight Per each 0.43

Uses, Certifications, and Standards

Application For Cutting Angle Iron, Pipe, Brass And Small Section Steel