

Bit Driver Sets

Ergonomic Bit Driver Set

Bayoneting ergonomic screwdriver with 6 bits in handle & Belt Pouch.

Includes a Screwdriver Handle, Insert Bit, 3 Slotted Bits, 3 Phillips Bits, Pouch.

Sizes of Bits are:

- Slotted: 0.6mm x 4.5mm, 1.0mm x 5.5mm, 1.2mm x 6.5mm



Part No.	Mfg. No.	Number of Pieces	Drive Size	Drive	Type
0256007	05051024002	8	1/4"	Phillips, Slotted	Bit Driver Set

Magnetic Bit Driver Set



Part No.	Mfg. No.	Number of Pieces	Drive Size	Drive
0297465	32510	32	5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16"	Hex

Insert Bit Sets

VEGA Industrial Driver Bit Sets



Image	Part No.	Mfg. No.	Number of Pieces	Contents
	0213479	V32-1P-SET	32	Phillips 0, 1, 2, 2R, 3; Slotted 3-4, 4-5, 6-8, 8-10, 10-12; TORX 10, 15, 20, 25, 27, 30, 40; Hex 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16; Square 1, 2, 3; Quick Release Bit Holder, Square Drive Bit Holder
	0213480	V32-1TP-SET	32	Phillips Security 2, 3; Spanner 4, 6, 8, 10, 12, 14; TORX Tamper 10, 15, 20, 25, 27, 30, 40; Hex Tamper 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16; Square 1, 2, 3; Quick Release Bit Holder, Square Drive Bit Holder
	0213481	V33-1SB	33	Phillips 1, 2, 3; TORX 10, 15, 20, 25, 30, 40; Slotted 4-5, 5-6, 6-8, 8-10, 10-12; Hex 5/64, 3/32, 1/8, 9/64, 5/32, 3/16; Square 1, 2, 3; 1/4x1/4 Socket Adapter; Chrome Sockets 3/16, 7/32, 1/4, 9/32, 5/16, 3/8, 7/16, 1/2; Quick Release Bit Holder
	0213482	V50-1P	50	Phillips 0, 1, 2, 3; Phillips ACR 0, 1, 2, 3; POZIDRIV 1, 2, 3; TORX 5, 6, 7, 8, 9, 10, 15, 20, 25, 27, 30, 40; Slotted 3-4, 4-5, 5-6, 6-8, 8-10, 10-12, 12-14, 14-16; Hex 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16; Square 0, 1, 2, 3;
	0213483	V50-1TP	50	Phillips ACR 0, 1, 2, 2R, 3; TORX Tamper 5, 6, 7, 8, 9, 10, 15, 20, 25, 27, 30, 40; Hex Tamper 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16; TRI-WING 2, 3, 4, 5; TORQ-SET 4, 6, 8, 10; Spline 4, 5, 6, 8; Clutch 5/32, 3/16, 1/4; Phillips
	0213484	VHS100A	100	Phillips 0, 1, 2, 2R, 3, 4; POZIDRIV 0, 1, 2, 3, 4; Square 0, 1, 2, 3, 4; TORX 6, 7, 8, 9, 10, 15, 20, 25, 27, 30, 40, 45, 50; Clutch 5/32, 3/16, 1/4; Hex 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16; Slotted 3-4, 4-5, 5-6, 6-8, 8-10,
	0213485	VSH53A	53	Phillips 1, 2, 3; Square 1, 2, 3; TORX 8, 10, 15, 20, 25, 27, 30, 40; TORX Tamper 8, 10, 15, 20, 25, 27, 30, 40; Clutch 5/32, 3/16, 1/4-Spline 5, 6, 8; TRI-WING 2, 3, 4, 5; TORQ-SET 6, 8, 10, 1/4; Spanner 4, 6, 8, 10, 12; Hex Tamper 7/64, 1/8, 5/32, 3/16

Milwaukee Shockwave Impact Driver Bit Sets



Image	Part No.	Mfg. No.	Number of Pieces	Contents
	0226446	48-32-4402	35	(12) 1" Insert Bits, (14) 2" Power Bits, (2) 3-1/2" Power Bits, (3) Magnetic Nut Drivers, (5) Hex Shank Drill Bits, Compact Magnetic Bit Holder, (2) Socket Adapters
	0254068	48-32-4401	29	Phillips bits: 1": P1, (7) P2, (2) P3, 2" Power, (2) P2, P3; Square bits: 1": SQ1, (4) SQ2, SQ3, 2" Power, (2) SQ2; Torx bits: 1": T15, T20, T25, 2" Power T25; Magnetic nut drivers: 1/4" red, 5/16" amber, 3/8" blue; magnetic bit holder, case with bulk st
	0259295	48-32-4403	18	3" Magnetic Drive Guide, (2) Phillips #2, Phillips #3, Square #2, Slotted 3/16", Slotted 1/4", ECX #1, ECX #2, Torx T15, Torx T20, Torx T25
	0259318	48-32-4615	7	T10, T15, T20, T25, T27, T30, T40 Insert Bits

Bit Sets



Image	Part No.	Mfg. No.	Number of Pieces	Contents
	0259220	05057687002	10	897/4 IMP R 1 x 1/4"X75; 868/1 IMP DC 1 x # 2x25; 868/1 IMP DC 1 x # 3x25; 851/1 IMP DC 1 x PH 2x25; 851/1 IMP 1 x PH 3x25; 855/1 IMP 1 x PZ 2x25; 855/1 IMP 1 x PZ 3x25; 867/1 1 x TX 25x25; 867/1 1 x TX 30x25; 867/1 1 x TX 40x25;
	0259222	05057686002	10	897/4 IMP R 1 x 1/4"X75; 868/1 IMP DC 6 x # 2x25; 868/1 IMP DC 3 x # 3x25
	0261160	05056372003	7	(6) Torx Bits, Adapter for Power Tools and Electronic Drills, Case
	0262156	05346291002	9	Assorted Bits, Bit Holder
	0262157	05346292002	9	(9) Phillips Bits, Ring Magnet Adapter for Power Tools and Electronic Drills, Case

Combination Screwdrivers



Combination Screwdrivers



Part No.	Mfg. No.	Brand Name	Size	Drive	Overall Length
0226252	32527	Klein	Slotted: 3/16", 1/4"; Phillips: #1, #2; Hex: 1/4", 5/16", 3/8"; Square: #1, #2	Hex, Phillips, Slotted, Square	7-1/2"
0227423	23932	Lenox	Phillips: #1, #2; Slotted: 1/4", 3/16"; Nut Driver: 1/4", 5/16", 3/8"; Square: #2, #3	Phillips, Slotted, Nut Driver	6-1/4"
0227424	23931	Lenox	Phillips: #1, #2; Slotted: 1/4", 3/16"; Nut Driver: 1/4", 5/16"	Phillips, Slotted, Nut Driver	6-1/4"
0244355	38016	WIHA	Slotted 4.5mm, 6.5mm; Phillips: #0, #1, #2, #3; Square: #1, #2	Phillips, Slotted, Square	9-1/2"
0244357	38018	WIHA	Slotted: 4.5mm, 5.5mm, 6.5mm, 8.0mm; Phillips: #0, #1, #2, #3	Phillips, Slotted	9-1/2"
0254067	48-22-2113	Milwaukee	7"	-	6-1/4"

TOOLS & EQUIPMENT