



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 49228510 Right Angle Attachment

*Milwaukee Electric Tool*

|                  |   |
|------------------|---|
| Catalog Number   | 49228510  |
| Manufacturer     | Milwaukee Electric Tool   |
| Description      | Drilling Holes and Installing Screws or Bolts In An Area Too Small For A Conventional Drill/Driver Can Exhaust The Patience Of The Most Experienced Contractor. When You Get Tired Of Using A Stubby Screwdriver You Can Either Shell Out The Big Bucks For A Right Angle Drill or You Can Save Your Money and Purchase Milwaukee'S Right Angle Attachment. Milwaukee Tool, One Of The Most Respected Names In The Tool Industry, Manufactures A 1/4 In. Hex Right Angle Attachment That Is Ideal For Cordless Drills Up to and |
| Weight per unit  | 1.1 (lbs/each)  |
| Product Category | Bits, Parts, Accessories  |

### Features

|                 |                                   |
|-----------------|-----------------------------------|
| Handle Included | Not Included                      |
| Handle Length   | 0.0                               |
| Material        | All-metal housing and steel gears |
| Shank Diameter  | 1/4 in                            |

### Material, Color, and Finish

|                 |     |
|-----------------|-----|
| Handle Material | n/a |
|-----------------|-----|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | RIGHT ANGLE ATTACHMENT  |
| extra long description | MILW 49-22-8510 Right Angle Drill A   |
| Features               | MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening,  |
| Long Description       | Drilling holes and installing screws or bolts in an area too small for a conventional drill/driver can exhaust the patience of the most experienced contractor. When you get tired of using a Stubby screwdriver you can either shell out the big bucks for a right angle drill or you can save your money and purchase Milwaukee's right angle attachment. Milwaukee Tool, one of the most respected names in the tool industry, manufactures a 1/4 in. hex right angle attachment that is ideal for cordless drills up to and |
| Product Type           | Right Angle Drill Attachment Kit  |
| Short Description      | Right AngleDRill Attachment Kt  |
| Special Features       | Compact Design Allows Work In Tight Areas; Durable All Metal Housing And Steel Gears; Rated Up To 235 In-Lbs Of Torque; Accepts Standard 1/4 In. Hex Shank Bits   |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Milwaukee®     |
| GTIN                      | 00045242183524 |
| Manufacturers Part Number | 49-22-8510     |
| UPC                       | 045242183524   |

## Taxonomies, Classifications, and Categories

|                      |             |
|----------------------|-------------|
| Category Description | HAND TOOLS  |
| Type                 | RIGHT ANGLE |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 10   |
| Weight Per each | 1.05 |

## Uses, Certifications, and Standards

|             |                     |
|-------------|---------------------|
| Application | For Cordless Drills |
|-------------|---------------------|