



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 48894603 3/32" Red Helix Titanium Drill Bit

*Milwaukee Electric Tool*

Catalog Number	48894603
Manufacturer	Milwaukee Electric Tool
Description	Milwaukee® Shockwave™ Impact Duty Titanium Drill Bits With Red Helix™ Are Engineered For Impacts and Drills. Designed With A Variable Helix™ With An Aggressive 35° Helix Angle Which Ends At 15°, The Impact Duty Titanium Drill Bits With Red Helix™ Provide Rapid Chip Removal™ to Limit Heat Buildup to Stay Sharper Longer™. The 135° Split Point Tip Delivers A Precision Start and Prevents Walking For Fast, Accurate Holes. Titanium Coating Can Be Used In All Drilling Applications to Give You Up to 3X Life VS. BL
Weight per unit	0.0450 (lbs/each)
Product Category	Bits, Parts, Accessories

### Features

Flute Length	0.740000
Shank Diameter	0.250000

### Dimensions and Weight

Length	2.38
--------	------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	3/32" RED HELIX TITANIUM DRILL BIT
extra long description	MILW 48-89-4603 3/32 In. Drill Bit
Features	MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening,
Long Description	Milwaukee® SHOCKWAVE™ Impact duty titanium drill bits with RED HELIX™ are engineered for impacts and drills. Designed with a Variable Helix™ with an aggressive 35° helix angle which ends at 15°, the impact duty titanium drill bits with RED HELIX™ provide Rapid Chip Removal™ to limit heat buildup to Stay Sharper Longer™. The 135° split point tip delivers a precision start and prevents walking for fast, accurate holes. Titanium coating can be used in all drilling applications to give you up to 3X life vs. BI
Product Type	3/32 In. Drill Bit

## Manufacturer Information

Brand	Milwaukee®
GTIN	00045242353040
Manufacturers Part Number	48-89-4603
UPC	045242353040

## Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
----------------------	-----------------------------

## Packaging

Carton	225
Package	5
Weight Per each	0.045