



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



49251261 Open-Lok 1-3/4" Titanium Enhanced Bi-Metal Blade

Milwaukee Electric Tool

| | |
|------------------|---|
| Catalog Number | 49251261 |
| Manufacturer | Milwaukee Electric Tool |
| Description | The Milwaukee® Open-Lok™ 1-3/4" Titanium Charged™ Bi-Metal Multi-Material Oscillating Multi-Tool Blades Are Made From Premium High-Speed Steel. These Bi-Metal Blades Are Ideal For Cuts In Wood, Nails, PVC, and Drywall. Titanium Charged™ Bi-Metal Blades Have An Optimized Titanium Blend For Maximum Wear-Resistance and Up to 15X Longer Life VS. High Carbon Steel (HCS) Blades. These Blades Feature A Reinforced Universal Fit Open-Lok™ Anchor For Better Strength & Control and Allow For Quick Blade Changes Across |
| Weight per unit | 0.0800 (lbs/each) |
| Product Category | Tools & Testers |

Features

| | |
|-----------------|------|
| Blade Length | 2.2 |
| Blade Thickness | 0.03 |
| Blade Width | 1.75 |

Material, Color, and Finish

| | |
|----------------|----------|
| Blade Material | Bi-Metal |
|----------------|----------|

Dimensions and Weight

| | |
|------|-------|
| Size | 1-3/4 |
|------|-------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | OPEN-LOK 1-3/4" TITANIUM ENHANCED BI-METAL BLADE |
| extra long description | MILW 49-25-1261 1-3/4" TITANIUM BI- |
| Features | MILWAUKEE® Oscillating Multi-Tool Accessories provide a complete solution for cutting, scraping, sanding and grinding across a wide range of materials and applications. Equipped with an OPEN-LOK™ Universal blade anchor for quick blade changes. Made with high quality materials and advanced manufacturing processes to deliver professional grade performance and market leading innovation. |
| Long Description | The MILWAUKEE® OPEN-LOK™ 1-3/4" TITANIUM CHARGED™ Bi-Metal Multi-Material Oscillating Multi-Tool Blades are made from premium high-speed steel. These bi-metal blades are ideal for cuts in wood, nails, PVC, and drywall. TITANIUM CHARGED™ Bi-Metal blades have an optimized titanium blend for maximum wear-resistance and up to 15x longer life vs. high carbon steel (HCS) blades. These blades feature a reinforced Universal Fit OPEN-LOK™ anchor for better strength & control and allow for quick blade changes across |
| Product Type | 1-3/4" Titanium Bi-Metal Blade 1PK |
| Short Description | 1-3/4" Titanm BI-METAL Bid 1PK |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Milwaukee® |
| GTIN | 00045242571055 |
| Manufacturers Part Number | 49-25-1261 |
| UPC | 045242571055 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------|
| Category Description | BITS, BLADES, AND HOLE SAWS |
| Type | Multi-Tool Blade |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 4 |
| Weight Per each | 0.08 |

Uses, Certifications, and Standards

| | |
|-------------|-------|
| Application | Metal |
|-------------|-------|