



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



5262WSP TVSS Recept 15A 125V Alarm WH

Pass & Seymour/LeGrand

Catalog Number	5262WSP
Manufacturer	Pass & Seymour/LeGrand
Description	Extra Heavy-Duty Surge Protective Duplex Receptacle Offers Increased Transient Protection, Reliability and Protection Notification (Audible Alarm With Led Indicator). Back and, Side Wire, 15AMP 125VOLT, White.
Weight per unit	0.3712 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	15
connection	Back and side wire
Material	Nylon
media	Yes
Number of Wires	3
Poles	2
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	#14 - #10

Material, Color, and Finish

Color	White
-------	-------

Dimensions and Weight

Height	3.75
Width	1.25



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	TVSS RECP 15A 125V ALARM WH
extra long description	P&S 5262WSP TVSS RECP 15A 125V ALAR
Long Description	Extra Heavy-Duty Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back and, Side Wire, 15amp 125volt, White.
Product Type	TVSS Recp 15A 125V Alarm WH
Special Features	Solid-state LED monitor has 25-year minimum life expectancy. A high visibility, wide-angle lens indicates protection is in place. LED Indication: steady green = protected, flashing red = not protected, OFF = no power to unit. Audible alarm alert of MOV damage. Alarm able to be turned On/Off. Wrap-around steel strap for structural integrity. Auto-ground is standard, for easier installation. Impact-resistant nylon exterior resists impacts and scrapes. Triple-wipe, copper-alloy contacts for superior, more dep

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007193893
Manufacturers Part Number	5262WSP
UPC	785007193893

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Spec Grade Surge Protective Receptacle, Audible Alarm with LED Indicator

Packaging

Carton	1
Package	50
Weight Per each	0.3712

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-15R
standard	ANSI/EEE C62.41 (Formerly IEEE 587), ANSI/IEEE C62.45 Installation Categories "A" (Ring Wave) "B" (Unidirectional Impulse).;CSA C22.2 No. 42;cUL UL1449, UL498
Temperature Rating	Operating Temperature: -20°C to +55°C (-4°F to 131°F), Storage Temperature: -40°C to +85°C (-40°F to 185°F)