



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



529 3/74" 1/4"-20 THRD 5/8" Jaw ZN PLT Beam Clamp

Crouse-Hinds

Catalog Number	529
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Rigid/Imc Beam Clamp/Insulator Support, 3/4" Base Size, 5/8" Jaw Opening Size, Malleable Iron, 1/4"-20 Tapped Holes
Weight per unit	0.1300 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

dimensions	1.1000 IN X 0.8800 IN X 1.2500 IN
Material	Malleable Iron

Material, Color, and Finish

Finish	Zinc Plated
--------	-------------

Dimensions and Weight

Size	3/4 in
------	--------

Descriptions

Description	3/74" 1/4"-20 THRD 5/8" JAW ZN PLT BEAM CLAMP
extra long description	MIDWEST 529 3/4 BEAM CLMP 1/4 20
Features	Crouse-Hinds series clamps, straps, clampbacks and hangers are used to secure rigid/IMC conduit to mounting surfaces or to provide space between conduit and its mounting surfaces. Available in a variety of materials to meet customer preferences, including steel, malleable iron, stainless steel and hot dip galvanized iron.
Long Description	Eaton Crouse-Hinds series rigid/IMC beam clamp/insulator support, 3/4" base size, 5/8" jaw opening size, Malleable iron, 1/4"-20 tapped holes
Product Type	3/4 Beam CLMP 1/4 20
Special Features	Jaw Opening Size 5/8 In, Load Capacity 230 Lb, Weight 13 Lb per 100

Manufacturer Information

Brand	Eaton
GTIN	00784564205292
UPC	784564205292

Taxonomies, Classifications, and Categories

Category Description	BEAM, RA, EDGE, & PARALLEL CLAMPS
Type	Beam clamp/insulator support



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	25
Weight Per each	0.13

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	UL, cUL