



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



54070 HBL 2G WP BX Extn RNG Gry

Hubbell--Raco

| | |
|------------------|---|
| Catalog Number | 54070 |
| Manufacturer | Hubbell--Raco |
| Description | 1-1/32 In. Deep Extension - 4-21/32 In. X 4-21/32 In. |
| Weight per unit | 0.4850 (lbs/each) |
| Product Category | Outlet Boxes, Etc. - Steel |

Features

| | |
|-----------------|----------|
| Knockouts | FALSE |
| Material | Aluminum |
| Packaging Type | Shrink |
| pallet quantity | 1500 |

Material, Color, and Finish

| | |
|-------|------|
| Color | Gray |
|-------|------|

Dimensions and Weight

| | |
|-------|-----------------------------|
| Depth | 1.0313 |
| Size | 4.656 H x 4.656 W x 1.031 D |
| Width | 4.656 |

Descriptions

| | |
|------------------------|--|
| Construction | Metallic |
| Description | HBL 2G WP BX EXTN RNG GRY |
| extra long description | RACO 5407-0 2G WP EXTENSION RING 1- |
| Features | Provides additional capacity needed for NEC box fill requirements. |
| Long Description | 1-1/32 In. Deep Extension - 4-21/32 In. x 4-21/32 In. |
| Product Type | Weatherproof Boxes & Extensions |
| Special Features | Weatherproof NEMA 3R rated, 1.031 IN deep, powder coat finish, installation hardware and gasket provided |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | BELL |
| GTIN | 00050169540701 |
| Manufacturers Part Number | 5407-0 |
| UPC | 050169540701 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------|
| Category Description | WEATHERPROOF BOXES & COVERS |
| Type | Extension/Adapter |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|------------------|-------|
| Carton | 1 |
| Standard Package | 10 |
| Weight Per each | 0.485 |

Uses, Certifications, and Standards

| | |
|-------------|--------------------------|
| Application | Accessory |
| standard | UL Listed; CSA Certified |