



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



63 1", 90D RGD Elb *Topaz - Southwire LLC*

Catalog Number	63
Manufacturer	Topaz - Southwire LLC
Description	Rigid Conduit Elbow, Steel Material; Galvanized Finish; UI (Canada and Us) Approval; Ansi C80.1 Applicable Standard; 20 Per Case Standard Package; 1 Inch Trade Size; Threaded End Type; 90 Degree Bend Angle; 5.75 Inch Bend Radius
Weight per unit	1.8 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

Applicable Standard	ANSI C80.1
Bend Angle	90 Degree
Bend Radius	5.75 INCH
End Type	THREADED
Material	Steel

Material, Color, and Finish

Finish	Galvanized
--------	------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Commodity Description	Rigid Conduit Fittings - Steel
Description	1", 90D RGD ELB
extra long description	GALVANIZED STEEL MATERIAL; HOT DIP GALVANIZED FINISH; UL (CANADA AND US), UL 6/E223147 APPROVAL; ANSI C80.1, FEDERAL SPECIFICATION WW-C-563 APPLICABLE STANDARD; 20 PER CASE STANDARD PACKAGE; 1 INCH TRADE SIZE; EXTERNAL THREADED END TYPE; 90 DEGREE BEND ANGLE; 5.75 INCH BEND RADIUS; APPLICATION SECURE CONNECTION TO RIGID CONDUIT, BEND ENABLES DIRECTIONAL CHANGES IN CONDUIT
Features	Topaz s Rigid 90 elbow is precision manufactured to deliver optimum safety and performance. Fabricated from galvanized steel for low conductivity and high corrosion resistance, all surfaces, both interior and exterior are defect free to ensure a secure connection to Rigid conduit and to preserve longevity. Available in sizes from 1/2 to 6 ; UL listed, HDG, meets Federal specification WW-C-563.
Long Description	RIGID CONDUIT ELBOW, STEEL MATERIAL; GALVANIZED FINISH; UL (CANADA AND US) APPROVAL; ANSI C80.1 APPLICABLE STANDARD; 20 PER CASE STANDARD PACKAGE; 1 INCH TRADE SIZE; THREADED END TYPE; 90 DEGREE BEND ANGLE; 5.75 INCH BEND RADIUS
Product Type	Rigid Conduit Elbow

Manufacturer Information

Brand	Southwire Rough Electrical Com
GTIN	00751338310506
UPC	751338310506

Taxonomies, Classifications, and Categories

Category Description	RIGID ELBOWS
----------------------	--------------

Trade Size

Trade Size	1 INCH
------------	--------

Packaging

Carton	20
Standard Package	20 PER CASE
Weight Per each	1.838

Uses, Certifications, and Standards

Approval	UL (CANADA AND US)
----------	--------------------