

E26 6" Trim Series


DESCRIPTION

Eyeball with 35° tilt max. trim with self-flange in the 6" trim family for use in recessed downlighting. Compatible for use in Halo and other housings.

| | | |
|-------------|--|------|
| Catalog # | | Type |
| Project | | |
| Comments | | Date |
| Prepared by | | |

SPECIFICATION FEATURES

- 35° Tilt max., 360° rotation
- Adjustable eyeball trim for BR30 and PAR30 lamps
- Torsion spring retention
- Socket supporting eyeball
- Self-flanged trim ring sized to hide gaps caused by construction tolerances



Dimensions:

A: 3-15/16" [100mm]
 H: 3-15/16" [100mm]
 OD: 7-3/4" [197mm]

| Housings | | Max Lamp Compatibility |
|----------|----------|----------------------------------|
| H7ICT | H7RICT | |
| H7ICAT | H7RICAT | 50W PAR30S, 75W PAR30L, 65W BR30 |
| E7ICAT | E7RICAT | |
| H7UICAT | | 75W PAR30S, 75W PAR30L, 65W BR30 |
| H7ICTNB | | |
| H7ICATNB | | 50W PAR30S, 75W PAR30L, 65W BR30 |
| E7ICATNB | | |
| H27ICAT | E27ICAT | 75W PAR30L, 65W BR30 |
| H27RICAT | E27RICAT | |
| H7T | E7TAT | 75W PAR30S, 75W PAR30L, 65W BR30 |
| H7TCP | | |
| H7RT | E7RTAT | 50W PAR30S, 75W PAR30L, 65W BR30 |
| H7TNB | E7TATNB | 75W PAR30S, 75W PAR30L, 65W BR30 |
| H27T | E27TAT | 50W PAR30S, 75W PAR30L, 65W BR30 |
| H27RT | E27RTAT | |

Compatible with Halogen, Incandescent, LED* or CFL* lamps.



6130WH
 White Eyeball,
 White Trim

6130

6-Inch Eyeball
 35° Tilt (Max.),
 Self-flange

ORDERING INFORMATION

SAMPLE NUMBER: 6130WH

| Trim | Finish |
|-------------------------------|---------------------------|
| 6130= 6" Eyeball, Self-flange | WH=White eyeball and trim |

HALO HOUSING COMPATIBILITY

| Trim # | Style | H7ICT | H7ICAT | H7RICT | H7RICAT | E7ICAT | E7RICAT | H7UICAT | H7ICTNB |
|--------|------------|----------|----------|---------|----------|---------|----------|---------|---------|
| 6130 | Adjustable | • | • | • | • | • | • | • | • |
| | | H7ICATNB | E7ICATNB | H27ICAT | H27RICAT | E27ICAT | E27RICAT | | |
| | | • | • | • | • | • | • | | |
| | | H7T | H7TCP | H7RT | E7TAT | E7RTAT | H7TNB | E7TATNB | H27T |
| • | • | • | • | • | • | • | • | • | |
| | | H27RT | E27TAT | E27RTAT | | | | | |
| • | • | • | | | | | | | |

For use in select other's housings, refer to U.L. classification list at www.eaton.com/lighting/legal.

*UL1993 listed LED & CFL equivalent lamps permitted. Consult lamp manufacturer for conditions of use. Eaton does not warranty the lamp.



For use in Halo listed housings.



Select trims are classified for use in other housings. See www.eaton.com/lighting/legal.

E26 6" Trim Series


DESCRIPTION

Eyeball with 35° tilt max. trim with self-flange in the 6" trim family for use in recessed downlighting. Compatible for use in Halo and other housings.

| | | |
|-------------|--|------|
| Catalog # | | Type |
| Project | | |
| Comments | | Date |
| Prepared by | | |

SPECIFICATION FEATURES

- 35° Tilt max., 360° rotation
- Adjustable eyeball trim for BR30 and PAR30 lamps
- Torsion spring retention
- Socket supporting eyeball
- Self-flanged trim ring sized to hide gaps caused by construction tolerances



Dimensions:

A: 3-15/16" [100mm]
 H: 3-15/16" [100mm]
 OD: 7-3/4" [197mm]

| Housings | | Max Lamp Compatibility |
|----------|----------|----------------------------------|
| H7ICT | H7RICT | |
| H7ICAT | H7RICAT | 50W PAR30S, 75W PAR30L, 65W BR30 |
| E7ICAT | E7RICAT | |
| H7UICAT | | 75W PAR30S, 75W PAR30L, 65W BR30 |
| H7ICTNB | | |
| H7ICATNB | | 50W PAR30S, 75W PAR30L, 65W BR30 |
| E7ICATNB | | |
| H27ICAT | E27ICAT | 75W PAR30L, 65W BR30 |
| H27RICAT | E27RICAT | |
| H7T | E7TAT | 75W PAR30S, 75W PAR30L, 65W BR30 |
| H7TCP | | |
| H7RT | E7RTAT | 50W PAR30S, 75W PAR30L, 65W BR30 |
| H7TNB | E7TATNB | 75W PAR30S, 75W PAR30L, 65W BR30 |
| H27T | E27TAT | 50W PAR30S, 75W PAR30L, 65W BR30 |
| H27RT | E27RTAT | |

Compatible with Halogen, Incandescent, LED* or CFL* lamps.



6130WH
 White Eyeball,
 White Trim

6130

6-Inch Eyeball
 35° Tilt (Max.),
 Self-flange

ORDERING INFORMATION

SAMPLE NUMBER: 6130WH

| Trim | Finish |
|-------------------------------|---------------------------|
| 6130= 6" Eyeball, Self-flange | WH=White eyeball and trim |

HALO HOUSING COMPATIBILITY

| Trim # | Style | H7ICT | H7ICAT | H7RICT | H7RICAT | E7ICAT | E7RICAT | H7UICAT | H7ICTNB |
|--------|------------|----------|----------|---------|----------|---------|----------|---------|---------|
| 6130 | Adjustable | • | • | • | • | • | • | • | • |
| | | H7ICATNB | E7ICATNB | H27ICAT | H27RICAT | E27ICAT | E27RICAT | | |
| | | • | • | • | • | • | • | | |
| | | H7T | H7TCP | H7RT | E7TAT | E7RTAT | H7TNB | E7TATNB | H27T |
| • | • | • | • | • | • | • | • | • | |
| | | H27RT | E27TAT | E27RTAT | | | | | |
| • | • | • | | | | | | | |

For use in select other's housings, refer to U.L. classification list at www.eaton.com/lighting/legal.

*UL1993 listed LED & CFL equivalent lamps permitted. Consult lamp manufacturer for conditions of use. Eaton does not warranty the lamp.



Select trims are classified for use in other housings. See www.eaton.com/lighting/legal.