

Project Name

Location

Prepared By



NUVO 62-5902

LED 9W LANDSCAPE FLOOD

Notes

(www) 09-22-2023 20:26:55

General

Status	Active
Finish	Bronze
Wattage	9W
Style	Utility
CCT (Kelvin)	2700K-5000K
Color Temperature	RGB and Tunable White
Length (in.)	6.25
Width (in.)	2.63
Height (in.)	4
Indoor or Outdoor Fixture	Outdoor

Smart Product Info

IOT Enabled	Yes
Integrated Camera	No
Communication Protocol	WiFi-2.4GHz
Voice Assistants Supported	Alexa; Google Home; Siri; SmartThings
Software Supported	Tuya/Starfish APP

Specifications

Technology	LED
CRI	90+
Lumen Output	800L
Rated Hours	50000
Voltage	120V
Dimmable	Yes-Dimmable
Dimming Note	Only with Starfish App
Beam Angle	60
Operating Temperature	-20C (-4F) to +40C (+104F)
Weight (lb.)	0.71
Fixture Material	Die-Cast Aluminum
Fixture Type	Flood Light

Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
Canadian Standard ICES-005	Class B
SDS Sheet	LED_Fixture

Additional Information

Includes	Die-Cast Mounting Plate
Warranty	5-Years

Project Name

Location

Prepared By



NUVO 62-5902

LED 9W LANDSCAPE FLOOD

Notes

(www) 09-22-2023 20:26:55

General

Status	Active
Finish	Bronze
Wattage	9W
Style	Utility
CCT (Kelvin)	2700K-5000K
Color Temperature	RGB and Tunable White
Length (in.)	6.25
Width (in.)	2.63
Height (in.)	4
Indoor or Outdoor Fixture	Outdoor

Smart Product Info

IOT Enabled	Yes
Integrated Camera	No
Communication Protocol	WiFi-2.4GHz
Voice Assistants Supported	Alexa; Google Home; Siri; SmartThings
Software Supported	Tuya/Starfish APP

Specifications

Technology	LED
CRI	90+
Lumen Output	800L
Rated Hours	50000
Voltage	120V
Dimmable	Yes-Dimmable
Dimming Note	Only with Starfish App
Beam Angle	60
Operating Temperature	-20C (-4F) to +40C (+104F)
Weight (lb.)	0.71
Fixture Material	Die-Cast Aluminum
Fixture Type	Flood Light

Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
Canadian Standard ICES-005	Class B
SDS Sheet	LED_Fixture

Additional Information

Includes	Die-Cast Mounting Plate
Warranty	5-Years