



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 65BEMWHLSSWW590CR 6" 12W Led Trim 1200LM Color Selectable

*Lithonia Lighting - Acuity*

Catalog Number	65BEMWHLSSWW590CR
Manufacturer	Lithonia Lighting - Acuity
Description	Experience The Ultimate 5-In-1 Solution With E Series Switchable White Led Trim Kits. Offering Flexibility At Your Fingertips, E Series Trim Kits Feature A Switch, Located Directly On The Fixture, That Allows You to Choose Between 5 Color Temperature Options Ranging From 2700K (Warm White) to 5000K (Daylight). Available In 5/6" Size, The E Series Provides Easy Retrofitting From Below The Ceiling or Can Be Paired With A Juno® Quick Connect QC Series Recessed Housing For New Construction Applications.
Weight per unit	0.7000 (lbs/each)
Product Category	Lighting

### Features

average life	50,000
dimensions	7.625 x 7.625 x 3.667
dimnable	Yes
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Dynamic
lumens	1200 LM,900 LM
Material	Aluminum
Number of Lamps	1
Reflector Type	Aluminum Spun
Shape	Round
Socket Type	N/A
Voltage Rating	120 V
Warranty	5
Wattage	13.9

### Material, Color, and Finish

Color	White
Finish	Matte
Style	CONTEMPORARY

### Dimensions and Weight

Height	4.125
Length	7.625
Width	7.625



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Construction	Retrofit
Description	6" 12W LED TRIM 1200LM COLOR SELECTABLE
extra long description	LITH 65BEMW HL SWW5 90CRI M6 6IN Ju
Features	Contractor Select
Long Description	Experience the ultimate 5-in-1 solution with E Series Switchable White LED Trim Kits. Offering flexibility at your fingertips, E Series Trim Kits feature a switch, located directly on the fixture, that allows you to choose between 5 color temperature options ranging from 2700K (Warm White) to 5000K (Daylight). Available in 5/6" size, the E Series provides easy retrofitting from below the ceiling or can be paired with a Juno® Quick Connect QC Series recessed housing for new construction applications.
Product Type	Trim
Special Features	Switchable Color Temperature

## Manufacturer Information

Brand	JUNO
GTIN	00194994244950
Manufacturers Part Number	65BEMW HL SWW5 90CRI M6
UPC	194994244950

## Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Trim

## Trade Size

aperture size	5 IN,6 IN
---------------	-----------

## Packaging

Carton	1
Package	6
Weight Per each	0.7

## Uses, Certifications, and Standards

Application	Hospitality,Residential,Retail,Retrofit
environmental conditions	Indoor,Outdoor
Mounting	Recessed
standard	CSAusCA Title 20,CA Title 24,ENERGY STAR,JA8