



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



691I Combo 15A 1 SW 1P-120V 1RECP-125V Iv

Pass & Seymour/Legrand

Catalog Number	691I
Manufacturer	Pass & Seymour/Legrand
Description	Our Standard Pass and Seymour Combination Switches Allow You to Add Lights to Any Room In Your Home Without Having to Add or Replace Wall Boxes.
Weight per unit	0.2171 (lbs/each)
Product Category	Combination Devices

Features

actuator	Toggle
amperage rating	15
connection	Side wire
Connection Type	Wired
Contact Rating	15 Amp, 120/125 VAC
indoor/outdoor	Indoor
Load Rating	15 A @ 120/125 VAC
Load Type	LED, Incandescent, Xenon, Universal, Fluorescent, Halogen, CFL
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Number of Wires	3
Outlet Type	Indoor
package quantity	1.0
Poles	1
supply voltage	120.0
Switch Type	Toggle
throw type	Single Throw
Voltage	120 VAC, 125 VAC
Voltage Rating	120/125
Wall Plate Included	NO
Wire Size	4

Material, Color, and Finish

Color	Ivory
Finish	SATIN

Dimensions and Weight

Size	3.3 in
------	--------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	COMBO 15A 1 SW 1P-120V 1RECP-125V IV
extra long description	P&S 691I COMBO 15A 1 SW 1P-120V 1RE
Features	Combination
Long Description	Our standard Pass and Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes.
Product Type	Combo 15A 1 SW 1P-120V 1RECP-125V I
Special Features	Two devices fits in one space, side wire

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007691016
Manufacturers Part Number	691-I
UPC	785007691016

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Switch, Combination, Outlet

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.2171

Uses, Certifications, and Standards

Application	Residential/Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-15R
standard	CULUS, UL 498