



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



692W Combo SW 1P 15A120V Pilot LT 1/25 GRD WH

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | 692W |
| Manufacturer | Pass & Seymour/Legrand |
| Description | 15 Amps, 120 Volts, Single Pole, Single Pilot Light, Combination Switch, Non-Grounding, White. |
| Weight per unit | 0.2000 (lbs/each) |
| Product Category | Combination Devices |

Features

| | |
|-----------------------|--------------------------|
| action | SP & Pilot Light |
| actuator | Toggle |
| amperage rating | 15 |
| connection | Side wire, non-grounding |
| Contact Configuration | N-O |
| Contact Rating | 120/125 VAC, 15 Amp |
| operating cycles | 30000 |
| Poles | 1 |
| Voltage Rating | 120/125 |
| Wattage | Pilot Light: 1/25 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | White |
|-------|-------|

Dimensions and Weight

| | |
|------|--------------------------|
| Size | 1.32 L x 0.94 W x 4.06 H |
|------|--------------------------|

Descriptions

| | |
|------------------------|---|
| Description | COMBO SW 1P 15A120V PILOT LT 1/25 GRD W |
| extra long description | P&S 692W COMBO SW 1P 15A120V PILOT |
| Long Description | 15 amps, 120 volts, Single Pole, Single Pilot Light, Combination Switch, Non-Grounding, White. |
| Product Type | Combo SW 1P 15A120V Pilot Lite 1/25 W |
| Special Features | Easily accessible break-off for separate or common feed. Long-life red neon lamp in pilot light rated 1/25 Watt, 125V. Side wire #12 and #14 AWG. Two devices fit into the space of one. |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007692020 |
| Manufacturers Part Number | 692W |
| UPC | 785007692020 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | Residential Switches |
| Type | COMBINATION |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|-----|
| Carton | 10 |
| Package | 50 |
| Weight Per each | 0.2 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Residential/Commercial |
| environmental conditions | Flammability: UL94 V2 |
| Mounting | WALL |
| Operating Temperature | Maximum continuous +60°C, minimum -30°C |
| standard | CULUS, UL20 |