

Metal Stud Punches



PRODUCT FEATURES

- Punch up through 20 gauge (0.9 mm) steel studs in one stroke.
- Aluminum head provides strength with minimum weight, reducing operator fatigue.
- Contoured handle design gives better operator leverage and makes it possible to punch in tight places.
- Self-stripping design eliminates punch hang-ups.
- Automatically centers holes on standard studs.
- Conversion kit available to upgrade early models from 24 gauge to 20 gauge maximum capacity.

SPECIFICATIONS

Capacity	709 - 1-5/8" (41.3 mm) and wider studs. 20 gauge (0.9 mm) steel studs. 710 - 2-1/2" (63.4 mm) and wider studs. 20 gauge (0.9 mm) steel studs.
Weight	709 - 7 lbs. (3.2 kg) 710 - 7.5 lbs (3.5 kg)

ORDERING INFORMATION

CAT NO.	UPC NO.	DESCRIPTION
709	22280	7/8" (22.2 mm) Diameter Stud Punch
710	21285	1-11/32" (34.1 mm) Diameter Stud Punch
30968	30968	Conversion Kit - Upgrades early model 709 or 710 from 24 to 20 gauge maximum capacity
121AV	04006	Punch for 709 - Accessory
22286	22286	Die for 709 - Accessory
24823	24823	Punch for 710 - Accessory
21297	21297	Die for 710 - Accessory
06015	06015	Repair Kit
36617	36617	Link



USA 800-435-0786 Fax: 800-451-2632
815-397-7070 Fax: 815-397-1865
Canada 800-435-0786 Fax: 800-524-2853
International +1-815-397-7070 Fax: +1-815-397-9247

4455 Boeing Drive • Rockford, IL 61109-2988 • USA • 815-397-7070
©2004 Greenlee Textron • An ISO 9001 Company • Printed in USA
Greenlee Textron is a subsidiary of Textron Inc.
www.greenlee.com MA-4691

Metal Stud Punches



PRODUCT FEATURES

- Punch up through 20 gauge (0.9 mm) steel studs in one stroke.
- Aluminum head provides strength with minimum weight, reducing operator fatigue.
- Contoured handle design gives better operator leverage and makes it possible to punch in tight places.
- Self-stripping design eliminates punch hang-ups.
- Automatically centers holes on standard studs.
- Conversion kit available to upgrade early models from 24 gauge to 20 gauge maximum capacity.

SPECIFICATIONS

Capacity	709 - 1-5/8" (41.3 mm) and wider studs. 20 gauge (0.9 mm) steel studs.
	710 - 2-1/2" (63.4 mm) and wider studs. 20 gauge (0.9 mm) steel studs.
Weight	709 - 7 lbs. (3.2 kg)
	710 - 7.5 lbs (3.5 kg)

ORDERING INFORMATION

CAT NO.	UPC NO.	DESCRIPTION
709	22280	7/8" (22.2 mm) Diameter Stud Punch
710	21285	1-11/32" (34.1 mm) Diameter Stud Punch
30968	30968	Conversion Kit - Upgrades early model 709 or 710 from 24 to 20 gauge maximum capacity
121AV	04006	Punch for 709 - Accessory
22286	22286	Die for 709 - Accessory
24823	24823	Punch for 710 - Accessory
21297	21297	Die for 710 - Accessory
06015	06015	Repair Kit
36617	36617	Link



USA 800-435-0786 Fax: 800-451-2632
815-397-7070 Fax: 815-397-1865
Canada 800-435-0786 Fax: 800-524-2853
International +1-815-397-7070 Fax: +1-815-397-9247

4455 Boeing Drive • Rockford, IL 61109-2988 • USA • 815-397-7070
©2004 Greenlee Textron • An ISO 9001 Company • Printed in USA
Greenlee Textron is a subsidiary of Textron Inc.
www.greenlee.com MA-4691