



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



693LA Disc Sub 693LAG, Rcd331a *Pass & Seymour/Legrand*

| | |
|------------------|--|
| Catalog Number | 693LA |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Double Three-Way Combination Switch, 15 Amps, 120/277 Volts, Light Almond. |
| Weight per unit | 0.2510 (lbs/each) |
| Product Category | Combination Devices |

Features

| | |
|-----------------------|--|
| action | (2) 3W |
| actuator | Toggle |
| amperage rating | 15 |
| connection | Side wire, non-grounding |
| Contact Configuration | N-O |
| Contact Rating | 15 Amp, 120/277 VAC |
| operating cycles | 30000 |
| Poles | 3-way |
| Voltage Rating | 0.43321299639 |
| Wattage | Electrical power is expressed in Amps and Volts. |

Dimensions and Weight

| | |
|------|--------------------------|
| Size | 1.32 L x 0.94 W x 4.06 H |
|------|--------------------------|

Descriptions

| | |
|------------------------|--|
| Description | DISC SUB 693LAG, RCD33LA |
| extra long description | P&S 693LA COMBO 2SWITCHES 3WAY 15A1 |
| Long Description | Double Three-way Combination Switch, 15 amps, 120/277 volts, Light Almond. |
| Product Type | Combo 2SWITCHES 3WAY 15A120/277V La |
| Special Features | Easily accessible break-off for separate or common feed. Side wire #12 and #14 AWG. Two devices fit into the space of one. |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007690194 |
| Manufacturers Part Number | 693LA |
| UPC | 785007690194 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Residential Switches |
| Type | Non-Grounding Combination Two Three-Way Switches |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status Inactive

Packaging

Carton 1

Package 10

Weight Per each 0.251

Uses, Certifications, and Standards

Application Residential/Commercial

environmental conditions Flammability: UL94 V2

Mounting WALL

Operating Temperature Maximum continuous +60°C, minimum -30°C

standard UL20