

E26 6" Trim Series


DESCRIPTION

Fresnel glass lens trim in the 6" trim family for use in recessed downlighting. Compatible for use in Halo and other housings.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

- White trim with glass Fresnel lens
- PS version features "dead-front" construction and is wet location listed for use in showers
- Non-conductive, non-corrosive polymer (plastic) trim ring
- Torsion spring retention




Dimensions:

OD: 8" [203mm]


Housings	Max Lamp Compatibility
H7UICAT	40W A19
H7T	H7TCP
H7RT	60W A19
E7TAT	
E7RTAT	
H27T	60W A19
H27TAT	

Compatible with Halogen, Incandescent, LED* or CFL* lamps.



73P

White Trim, Fresnel Glass Lens



73PS

White Trim, Fresnel Glass Lens,
Wet Location Listed

73

ORDERING INFORMATION

SAMPLE NUMBER: 73PS

Trim	Finish
73P= 6" Drop Opal Glass Lens, White Trim	WH=White Trim
73PS= 6" Drop Opal Glass Lens, White Polymer Trim, Wet Location	WH=White Trim

HALO HOUSING COMPATIBILITY

Trim #	Style	H7ICT	H7ICAT	H7RICT	H7RICAT	E7ICAT	E7RICAT	H7UICAT	H7ICTNB
73P 73PS	Showerlight							•	
		H7ICATNB	E7ICATNB	H27ICAT	H27RICAT	E27ICAT	E27RICAT		
		H7T	H7TCP	H7RT	E7TAT	E7RTAT	H7TNB	E7TATNB	H27T
		•	•	•	•	•			•
		H27RT	E27TAT	E27RTAT					
			•						

For use in select other's housings, refer to U.L. classification list at www.eaton.com/lighting/legal.

*UL1993 listed LED & CFL equivalent lamps permitted. Consult lamp manufacturer for conditions of use. Eaton does not warranty the lamp.

Showerlight

UL US
LISTED

For use in Halo listed housings.

CLASSIFIED
UL US

Select trims are classified for use in others housings.
See www.eaton.com/lighting/legal.

E26 6" Trim Series


DESCRIPTION

Fresnel glass lens trim in the 6" trim family for use in recessed downlighting. Compatible for use in Halo and other housings.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

- White trim with glass Fresnel lens
- PS version features "dead-front" construction and is wet location listed for use in showers
- Non-conductive, non-corrosive polymer (plastic) trim ring
- Torsion spring retention




Dimensions:

OD: 8" [203mm]


Housings	Max Lamp Compatibility
H7UICAT	40W A19
H7T	H7TCP
H7RT	60W A19
E7TAT	
E7RTAT	
H27T	60W A19
H27TAT	

Compatible with Halogen, Incandescent, LED* or CFL* lamps.



73P

White Trim, Fresnel Glass Lens



73PS

White Trim, Fresnel Glass Lens,
Wet Location Listed

73

ORDERING INFORMATION

SAMPLE NUMBER: 73PS

Trim	Finish
73P= 6" Drop Opal Glass Lens, White Trim	WH=White Trim
73PS= 6" Drop Opal Glass Lens, White Polymer Trim, Wet Location	WH=White Trim

HALO HOUSING COMPATIBILITY

Trim #	Style	H7ICT	H7ICAT	H7RICT	H7RICAT	E7ICAT	E7RICAT	H7UICAT	H7ICTNB
73P 73PS	Showerlight							•	
		H7ICATNB	E7ICATNB	H27ICAT	H27RICAT	E27ICAT	E27RICAT		
		H7T	H7TCP	H7RT	E7TAT	E7RTAT	H7TNB	E7TATNB	H27T
		•	•	•	•	•			•
		H27RT	E27TAT	E27RTAT					
			•						

For use in select other's housings, refer to U.L. classification list at www.eaton.com/lighting/legal.

*UL1993 listed LED & CFL equivalent lamps permitted. Consult lamp manufacturer for conditions of use. Eaton does not warranty the lamp.

Showerlight

UL
C US
LISTED

For use in Halo listed housings.

CLASSIFIED
UL
C US

Select trims are classified for use in others housings.
See www.eaton.com/lighting/legal.