



## ADJUSTABLE FAR-SIDE BOX SUPPORT, BACK MOUNT, 2 1/2", 3 1/2", 4", 6" WALL DEPTH

### CATALOG NUMBER

---

**766A**



### CERTIFICATIONS

---



### FEATURES

---

Provides far side electrical box support in various stud wall depths

### PRODUCT ATTRIBUTES

---

Material: Steel

Finish: Pregalvanized

Box Depth: 1 1/4"; 2 1/8"

Stud Wall Depth: 2 1/2" - 3 1/2"; 4" Min

### ADDITIONAL PRODUCT DETAILS

---

No load rating, for positioning only.

### WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction,

property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**



## ADJUSTABLE FAR-SIDE BOX SUPPORT, BACK MOUNT, 2 1/2", 3 1/2", 4", 6" WALL DEPTH

### CATALOG NUMBER

**766A**



### CERTIFICATIONS



### FEATURES

Provides far side electrical box support in various stud wall depths

### PRODUCT ATTRIBUTES

Material: Steel

Finish: Pregalvanized

Box Depth: 1 1/4"; 2 1/8"

Stud Wall Depth: 2 1/2" - 3 1/2"; 4" Min

### ADDITIONAL PRODUCT DETAILS

No load rating, for positioning only.

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction,

property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

**Europe**

Netherlands:

+31 800-0200135

France:

+33 800 901 793

**Europe**

Germany:

800 1890272

Other Countries:

+31 13 5835404

**APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**