



**GREENLEE®**

A Textron Company

*New & Improved*

# Hole Saws



**SUPERIOR  
CUTTING  
POWER**



# GREENLEE®

A Textron Company



## Engineered To Be The Best!

Greenlee is proud to introduce our new and improved Hole Saws. These Hole Saws were designed to cut faster, last longer and provide even greater value than before. The new and improved Greenlee Hole Saw cuts **up to 30% faster than the competition** – saving you time and money on the job.

In addition to the oxide finish, the Greenlee Hole Saws are clearly marked for easy size identification and includes the part number for convenient reorder reference.

### Applications



Electrical Box



Angled Metal



Wood

# 3

### Reasons to buy Greenlee's New & Improved Hole Saws

The new robust tooth design is made from a higher quality steel that's fully hardened for a stronger, more durable saw that's tough enough to cut through the most demanding cutting applications.

Finally, Greenlee Hole Saws can be used with the Greenlee removable depth stop (826S) for added protection when cutting in areas where wires may be present, and with the Quick Change arbor for fast and easy changeovers.

Give them a try and you will see that we have made a great product even better. Just more ways Greenlee is there with you, helping get the job done faster, safer and easier.


A key feature of Greenlee Hole Saws has always been its oxide finish. The oxide finish resists rust and chip build-up for easier cutting. There is no paint on the saw that melts while cutting – so there's no paint gum-up or possible smoke when heated.



**TIME = MONEY on the jobsite.**

# 1 Cuts 30% Faster Than The Competition!\*

Cut Times By Brand: 1-1/8" Hole Saw



\*Based on independent testing 1-1/8" hole saw, 14 gauge steel, 800 rpm, 50lb load measured at cutting surface.

## **2** Stronger & more durable than ever before.

*4-6 variable pitch for smoother cutting*

*Teeth stay sharp longer for faster, cleaner cuts*

*Saws clearly marked for easy size identification*

*Thicker backplate for a more rigid longer lasting saw*

*Fully hardened tooth for stronger, more durable saw*

*Added Safety with removable depth stop (#826S)*

*Oxide finish resists rust and chip buildup for easier cutting*

*Fast and easy change-overs using Quick Change Arbor*

## **3** More Features

*Only Greenlee offers these exclusive features & accessories to make the job faster, safer and easier.*

- Quick Change Arbor
- Removable Depth Stop
- Oxide Finish



**SUPERIOR  
CUTTING  
POWER**

**See Back For  
Ordering Information.**



# Ordering Information

**R** = REPLACEMENT PART **A** = ACCESSORY

Cat No.	UPC	Description	Qty
825-9/16	19131	HOLESAW,VARIABLE PITCH (9/16")	1
825-5/8	19132	HOLESAW,VARIABLE PITCH (5/8")	1
825-11/16	19133	HOLESAW,VARIABLE PITCH (11/16")	1
825-3/4	19134	HOLESAW,VARIABLE PITCH (3/4")	1
825-13/16	19135	HOLESAW,VARIABLE PITCH (13/16")	1
825-7/8	19136	HOLESAW,VARIABLE PITCH (7/8")	1
825-15/16	19137	HOLESAW,VARIABLE PITCH (15/16")	1
825-1	19138	HOLESAW,VARIABLE PITCH (1")	1
825-1-1/16	19140	HOLESAW,VARIABLE PITCH (1 1/16")	1
825-1-1/8	19141	HOLESAW,VARIABLE PITCH (1 1/8")	1
825-1-3/16	19143	HOLESAW,VARIABLE PITCH (1 3/16")	1
825-1-1/4	19144	HOLESAW,VARIABLE PITCH (1 1/4")	1
825-1-5/16	19145	HOLESAW,VARIABLE PITCH (1 5/16")	1
825-1-3/8	19146	HOLESAW,VARIABLE PITCH (1 3/8")	1
825-1-7/16	19147	HOLESAW,VARIABLE PITCH (1 7/16")	1
825-1-1/2	19148	HOLESAW,VARIABLE PITCH (1 1/2")	1
825-1-9/16	19149	HOLESAW,VARIABLE PITCH (1 9/16")	1
825-1-5/8	19150	HOLESAW,VARIABLE PITCH (1 5/8")	1
825-1-11/16	19151	HOLESAW,VARIABLE PITCH (1 11/16")	1
825-1-3/4	19152	HOLESAW,VARIABLE PITCH (1 3/4")	1
825-1-13/16	19153	HOLESAW,VARIABLE PITCH (1 13/16")	1
825-1-7/8	19154	HOLESAW,VARIABLE PITCH (1 7/8")	1
825-2	19155	HOLESAW,VARIABLE PITCH (2")	1
825-2-1/16	19157	HOLESAW,VARIABLE PITCH (2 1/16")	1
825-2-1/8	19158	HOLESAW,VARIABLE PITCH (2 1/8")	1
825-2-1/4	19159	HOLESAW,VARIABLE PITCH (2 1/4")	1
825-2-5/16	19160	HOLESAW,VARIABLE PITCH (2 5/16")	1
825-2-3/8	19161	HOLESAW,VARIABLE PITCH (2 3/8")	1
825-2-1/2	19162	HOLESAW,VARIABLE PITCH (2 1/2")	1
825-2-9/16	19163	HOLESAW,VARIABLE PITCH (2 9/16")	1
825-2-5/8	19164	HOLESAW,VARIABLE PITCH (2 5/8")	1
825-2-3/4	19165	HOLESAW,VARIABLE PITCH (2 3/4")	1
825-2-7/8	19166	HOLESAW,VARIABLE PITCH (2 7/8")	1
825-3	19167	HOLESAW,VARIABLE PITCH (3")	1
825-3-1/8	19168	HOLESAW,VARIABLE PITCH (3 1/8")	1
825-3-1/4	19169	HOLESAW,VARIABLE PITCH (3 1/4")	1
825-3-3/8	19170	HOLESAW,VARIABLE PITCH (3 3/8")	1
825-3-1/2	19171	HOLESAW,VARIABLE PITCH (3 1/2")	1
825-3-5/8	19172	HOLESAW,VARIABLE PITCH (3 5/8")	1
825-3-3/4	19174	HOLESAW,VARIABLE PITCH (3 3/4")	1
825-3-7/8	19175	HOLESAW,VARIABLE PITCH (3 7/8")	1
825-4	19176	HOLESAW,VARIABLE PITCH (4")	1
825-4-1/8	19177	HOLESAW,VARIABLE PITCH (4 1/8")	1
825-4-1/4	19178	HOLESAW,VARIABLE PITCH (4 1/4")	1
825-4-3/8	19179	HOLESAW,VARIABLE PITCH (4 3/8")	1
825-4-1/2	19180	HOLESAW,VARIABLE PITCH (4 1/2")	1
825-4-3/4	19181	HOLESAW,VARIABLE PITCH (4.75")	1
825-5	19182	HOLESAW,VARIABLE PITCH (5")	1
825-5-1/2	19183	HOLESAW,VARIABLE PITCH (5.5")	1
825-6	19184	HOLESAW,VARIABLE PITCH (6")	1
825-68	36169	HOLESAW,VARIABLE PITCH (68,0 MM)	1
825-74	36170	HOLESAW,VARIABLE PITCH (70,0 MM)	1

Cat No.	UPC	Description	Qty
<b>KITS</b>			
830PG	29209	HOLESAW SET	1
830Q	2806	HOLESAW KIT (830Q)	1
830QS	10915	HOLESAW KIT	1
830S	10912	HOLESAW SET	1
830	19192	HOLESAW SET	1
834	19913	HOLESAW SET	1
835	27538	HOLESAW KIT	1
889	3478	HOLESAW KIT,PLUMBERS (889)	1
890	3479	HOLESAW KIT,INDUSTRIAL MAINT (89)	1
891	3480	HOLESAW KIT-ELECTRICIAN/PLUMBER(	1
<b>ACCESSORIES</b>			
826S	12787	<b>A</b> HOLESAW STOP-3 PAK (POP)	1
38522	38522	<b>A</b> ARBOR, .312 HEX (PKG)	1
2800	2800	<b>A</b> ARBOR, QUICK CHANGE-5/16	1
2801	2801	<b>A</b> ARBOR, QUICK CHANGE-7/16	1
37154	37154	<b>A</b> ARBOR,3/8" SHANK W/3 FLATS (PKG)	1
37156	37156	<b>A</b> ARBOR,HOLESAW 1/2 SHANK W/3 FLAT	1
38506	38506	<b>A</b> ARBOR,HOLESAW 1/2" SHANK W/3 FLA	1
37155	37155	<b>A</b> ARBOR,HOLESAW 7/16 HEX (PKG,371	1
37157	37157	<b>A</b> ARBOR,HOLESAW SMALL (PKG, 37157	1
38507	38507	<b>A</b> ARBOR,HOLESAW-SMALL	1
38524	38524	<b>A</b> ARBOR-.312 HEX BLST PKGD	1
38505	38505	<b>A</b> ARBOR-HOLESAW .437 HEX	1
38504	38504	<b>A</b> ARBOR-HOLESAW 3/8" SHANK W/3 FLA	1
39873	39873	<b>R</b> DRILL,PILOT (39873).	1
37623	37623	<b>R</b> DRILL-PILOT (HOLESAW).	1
39893	39893	<b>A</b> DRILL-PILOT .250X3.25LG.	1
38526	38526	<b>A</b> DRILL-PILOT PKGD	1



**New clamshell packaging provides more merchandising visibility**

