



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



774010 Toggle Switch, SPST, On-Off, O-Ring, Screw

Ideal

| | |
|------------------|--|
| Catalog Number | 774010 |
| Manufacturer | Ideal |
| Description | Toggle Switch, 1 Pole, 10 A;20 A, 125/227 V Ac, SPST Contact Configuration, Solid Brass;Nickel-Plated (Bushing) Material, Spade Connection, Hole Mount, Nickel Plated (Bushing), 1.130 In (L) X 0.570 In (W) X 0.610 In (H), +32 °F Operating Temperature, +185 °F Operating Temperature, 0.1 LB |
| Weight per unit | 0.1000 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|------------------|---|
| action | SPST |
| actuator | Toggle |
| amperage rating | 10/20 |
| connection | Spade, 2 Terminals |
| Contact Rating | Factory Tested 100000 Cycles To 21 AMP 14.8 VDC DC Rating |
| operating cycles | 100k |
| Poles | 1 |

Dimensions and Weight

| | |
|------|--|
| Size | 1.130 IN Length X 0.570 IN Width X 0.610 IN Height |
|------|--|

Descriptions

| | |
|-------------|--|
| Description | TOGGLE SWITCH, SPST, ON-OFF, O-RING,SCREW |
| Features | Great for power tool and motor control switch applicationsRugged long-wearing solid brass/nickel-plated bushings1/2 in. diameter mounting holeDielectric Strength: 1500VMechanical Life: 100,000 cyclesOperating Temperature: 32°F to 185°F (0°C to 85°C)DC?Rating: Factory tested 100,000 cycles to 21 Amp 14.8 VDC |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Ideal |
| GTIN | 00783250573431 |
| UPC | 783250573431 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------|
| Category Description | TOGGLE SWITCHES |
| Type | Standard, On-Off |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 0.1 |

Uses, Certifications, and Standards

| | |
|-----------------------|----------------------|
| Mounting | 1/2 IN Hole Diameter |
| Operating Temperature | 32 To 185 |
| standard | CSA, RU Listed, RoHS |