




## B18-Z BOX/CONDUIT HANGER WITH ROD/WIRE CLIP, 1/2", 3/4" EMT, 1/4" ROD, #12 WIRE

### CATALOG NUMBER

**812MB18**



### CERTIFICATIONS



### FEATURES

One assembly provides support for electrical box and/or conduit from drop wire or rod

Eliminates need for offset bending conduit

66% less Drop Wires (rod/wire application)

NEC® & CEC compliant

Increased capability and application options by combining 4Z and 6Z products into one enhanced and efficient offering

Improved multi-function clip allows for optimized inventory while reducing job site scheduling risks associated with multiple SKUs

### PRODUCT ATTRIBUTES

Material: Spring Steel

Finish: nVent CADDY Armour

EMT Conduit Size: 1/2";3/4"

Outer Diameter: 0.710" - 1.18"

Rod Size: 1/4",3/8"

Wire Size: #12

## ADDITIONAL PRODUCT DETAILS

---

NEC® 300.11 requires dedicated drop wire/rod. For single and multiple runs of conduit.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500




Our powerful portfolio of brands:  
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**



## B18-Z BOX/CONDUIT HANGER WITH ROD/WIRE CLIP, 1/2", 3/4" EMT, 1/4" ROD, #12 WIRE

### CATALOG NUMBER

**812MB18**



### CERTIFICATIONS



### FEATURES

One assembly provides support for electrical box and/or conduit from drop wire or rod

Eliminates need for offset bending conduit

66% less Drop Wires (rod/wire application)

NEC® & CEC compliant

Increased capability and application options by combining 4Z and 6Z products into one enhanced and efficient offering

Improved multi-function clip allows for optimized inventory while reducing job site scheduling risks associated with multiple SKUs

### PRODUCT ATTRIBUTES

Material: Spring Steel

Finish: nVent CADDY Armour

EMT Conduit Size: 1/2";3/4"

Outer Diameter: 0.710" - 1.18"

Rod Size: 1/4",3/8"

Wire Size: #12

## ADDITIONAL PRODUCT DETAILS

---

NEC® 300.11 requires dedicated drop wire/rod. For single and multiple runs of conduit.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**