



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 8824GRTNK 8X8X24 N3R Wireway

Unity MFG

|                  |  |
|------------------|--|
| Catalog Number   | 8824GRTNK  |
| Manufacturer     | Unity MFG  |
| Description      | Slip-On Cover Trough, Slip On, Gray, Low Carbon Steel, 24 In Overall Length, 8 In Overall Height, 8 In Overall Width, Powder Coated, 15 LB |
| Weight per unit  | 15.0 (lbs/each)  |
| Product Category | Nema Type 3R Trough & Gutter   |

### Features

|           |    |
|-----------|----|
| Knockouts | NO |
|-----------|----|

### Dimensions and Weight

|        |    |
|--------|----|
| Depth  | 8  |
| Length | 24 |
| Width  | 8  |

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 8X8X24 N3R WIREWAY   |
| extra long description | UNT 8824GRTNK N3R SCREW COVER GUTTE  |
| Special Features       | For protecting wiring indoors from dripping water, or outdoors from rain, sleet and snow; Formed from code gauge, low carbon steel; Drip shield top, seam-free sides; Accumulation-free bottom; Embossed mounting holes provided; Slip-on cover without gasket |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Unity          |
| GTIN  | 00761515143094 |
| UPC   | 761515143094   |

### Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | STEEL WIRE WAY JUNCTION BOXES          |
| Type                 | GRT Gutter Slip-On Cover Wiring Trough |

### Packaging

|                 |    |
|-----------------|----|
| Carton          | 1  |
| Weight Per each | 15 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Enclosure  
standard

NEMA 3R, IP32

UL 50 And UL 870 - Type 3R: Intended For Outdoor Use Primarily To Provide A Degree Of Protection Against Rain, Sleet And Damage From External Ice Formation, CSA C22.2 No. 26 Certified, Type 3R, IEC 60529, RoHS Compliant