

# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685



# **885TRBK Radiant 15A 125V TR Duplex Recp BK** Pass & Seymour/Legrand

Catalog Number	885TRBK
Manufacturer	Pass & Seymour/Legrand
Description	Take A Step Up From The Standard. This Tamper-Resistant Duplex Outlet Installs Easily For The Basic Power Every Home Needs, While Elevating Your Space With The Sleek, Clean Lines Of Radiant Registered For A Sophisticated Look. Made Exclusively For Use With Screwless Wall Plates From The Radiant Registered Collection, Sold Separately.
Weight per unit	0.1408 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro
Features	
gang	1
indoor/outdoor	Indoor
insulation	False
media	Yes
Mounting Type	Box
Number of Wires	3
orientation	Vertical
Outlet Type	Tamper-Resistant
Poles	2
Voltage	125.0 V, 120.0 V
Wall Plate Included	NO
Material, Color, and Finish	
Finish	Matte
Dimensions and Weight	
Size	4.2"
Thickness	1.3"



# ELLIOTT ELECTRIC SUPPLY 2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

-				•	
. 1	es	~ri	nt	10	nc
_		<b>UI</b> I	$\sim$ $\cdot$		

P&S 885TRBK RADIANT 15A/125V TR DUP
Description Challe
Decorator Style
Take a step up from the standard. This tamper-resistant duplex putlet installs easily for the basic power every home needs, while elevating your space with the sleek, clean lines of radiant Registered for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.
Radiant 15A/125V TR Dup Recep BK
amper resistant, quick loop wire aid, extra long strap, side access, push wire

#### **Manufacturer Information**

Brand	Pass and Seymour
GTIN	00785007861044
Manufacturers Part Number	885-TRBK
UPC	785007861044

## **Taxonomies, Classifications, and Categories**

Category Description	Residential receptacles
Type	Outlet
5.	

### **Trade Size**

Amperage 15.0	
---------------	--

## **Packaging**

Carton	10
Package	200
Weight Per each	0.1408

### Uses, Certifications, and Standards

Application	Residential/Commercial
environmental conditions	95% (relative humidity, non-condensing)
Mounting	WALL
nema rating	15A
standard	UL, CULUS, UL 498