



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

800 Old Boston Road
75501-0000, TX Texarkana
Phone: 903-223-6400
Fax: 903-223-6700



885GRY Radiant 15A 125V Duplex Recept Gy

Pass & Seymour/LeGrand

Catalog Number	885GRY
Manufacturer	Pass & Seymour/LeGrand
Description	Take A Step Up From The Standard. This Duplex Outlet Installs Easily For The Basic Power Every Home Needs, While Elevating Your Space With The Sleek, Clean Lines Of Radiant Registered For A Sophisticated Look. Made Exclusively For Use With Screwless Wall Plates From The Radiant Registered Collection, Sold Separately.
Weight per unit	0.1400 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

gang	2
indoor/outdoor	Indoor
insulation	False
media	Yes
Mounting Type	Box
Number of Gangs	1.0
Number of Wires	3
orientation	Vertical
Outlet Type	Tamper-Resistant, Straight Blade
Poles	2
Voltage	120.0 V, 125.0 V
Wall Plate Included	NO

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	4.25"
Thickness	1.3"



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

800 Old Boston Road
75501-0000, TX Texarkana
Phone: 903-223-6400
Fax: 903-223-6700

Descriptions

Description	RADIANT 15A 125V DUPLEX RECP GY
extra long description	P&S 885GRY RADIANT 15A/125V DUP REC
Features	Decorator Style
Long Description	Take a step up from the standard. This duplex outlet installs easily for the basic power every home needs, while elevating your space with the sleek, clean lines of radiant Registered for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.
Product Type	Radiant 15A/125V Dup Recep Gry
Special Features	High impact resistant, extra long strap, quick loop wire aid, long term blade retention

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007885088
Manufacturers Part Number	885-GRY
UPC	785007885088

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Outlet

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	10
Package	200
Weight Per each	0.14

Uses, Certifications, and Standards

Application	Residential/Commercial
environmental conditions	95% (relative humidity, non-condensing)
Mounting	WALL
nema rating	15A
standard	UL, CULUS, UL 498