



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



94215W 4 Speed Iv Fan Control

Pass & Seymour/Legrand

Catalog Number	94215W
Manufacturer	Pass & Seymour/Legrand
Description	Fan Speed Control Switch, 4-Speed, 2-Level Type; 1.67 Inch W X 1.43 Inch D X 4.15 Inch H Size; White Color; UI, Csa Approval; Residential Application; 120 V Voltage Rating; 15 Ampere 300 W Load Rating; Rotary, Hi/Low Dimmer, Decorator Operator Type
Weight per unit	0.3500 (lbs/each)
Product Category	Fan Speed Switches & Controls

Features

Load Rating	15 Ampere 300 W
Load Type	Solid State Fan
Operator Type	Rotary, Hi/Low Dimmer, Decorator
Voltage Rating	120 V

Material, Color, and Finish

Color	White
-------	-------

Dimensions and Weight

Size	1.67 Inch W x 1.43 Inch D x 4.15 Inch H
------	---

Descriptions

Additional Information	Applicable Standard NEMA WD1/WD6
Commodity Description	FAN SPEED SWITCHES & CONTROLS
Description	4 SPEED IV FAN CONTROL
Long Description	FAN SPEED CONTROL SWITCH, 4-SPEED, 2-LEVEL TYPE; 1.67 INCH W X 1.43 INCH D X 4.15 INCH H SIZE; WHITE COLOR; UL, CSA APPROVAL; RESIDENTIAL APPLICATION; 120 V VOLTAGE RATING; 15 AMPERE 300 W LOAD RATING; ROTARY, HI/LOW DIMMER, DECORATOR OPERATOR TYPE
Product Type	Fan Speed Control Switch

Manufacturer Information

Brand	Pass and Seymour
Manufacturers Part Number	94215-W
Model	94

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	4-Speed, 2-Level



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Manufacturer Status	Non-Stock
Status	Inactive

Packaging

Carton	1
Package	24
Weight Per each	0.35

Uses, Certifications, and Standards

Application	Residential
Approval	UL, CSA