

Socket Extenders & Adapters



92-408
Candelabra to Candelabra
E12 - E12 Extender
Overall Ext. 5/8"
75W-120V
Non-UL



92-405
Candelabra to Intermediate
E12 - E17 Extender
Overall Ext. 1/2"
75W-120V
Non-UL



90-1519
Candelabra to Medium
E12 - E26
Overall Ext. 1"
75W-120V
Non-UL



92-407
French to Intermediate
E14 - E17 Extender
Overall Ext. 1/2"
75W-120V
Non-UL



90-1801
Mogul to Mogul
E39 - E39 Extender
4KV - Porcelain
Overall Ext. 2 3/8" - 2 1/4" Dia.
1500W-600V



92-323
Medium to Medium
E26 - E26 Extender
Phenolic
Overall Ext. 1"
660W-250V



92-324
Medium to Medium
E26 - E26 Extender
Porcelain
Overall Ext. 1"
660W-250V



90-2589
Medium to Medium E26 - E26
2 Piece Glazed Porcelain Extender
Overall Ext. 1 1/4"
660W-250V



90-446 Brown
90-2451 Ivory
Medium Base
Pull Chain Current Tap
660W-125V



90-2449 Brown
90-2450 Ivory
Medium Base
Keyless Current Tap
660W-125V



90-1121 Brown
90-2465 Ivory
Single to Twin Lampholder
Overall Height 2 3/4" - Ext. 2"
660W Max. Total-250V



Socket Extenders & Adapters



92-408
Candelabra to Candelabra
E12 - E12 Extender
Overall Ext. 5/8"
75W-120V
Non-UL



92-405
Candelabra to Intermediate
E12 - E17 Extender
Overall Ext. 1/2"
75W-120V
Non-UL



90-1519
Candelabra to Medium
E12 - E26
Overall Ext. 1"
75W-120V
Non-UL



92-407
French to Intermediate
E14 - E17 Extender
Overall Ext. 1/2"
75W-120V
Non-UL



90-1801
Mogul to Mogul
E39 - E39 Extender
4KV - Porcelain
Overall Ext. 2 3/8" - 2 1/4" Dia.
1500W-600V



92-323
Medium to Medium
E26 - E26 Extender
Phenolic
Overall Ext. 1"
660W-250V



92-324
Medium to Medium
E26 - E26 Extender
Porcelain
Overall Ext. 1"
660W-250V



90-2589
Medium to Medium E26 - E26
2 Piece Glazed Porcelain Extender
Overall Ext. 1 1/4"
660W-250V



90-446 Brown
90-2451 Ivory
Medium Base
Pull Chain Current Tap
660W-125V



90-2449 Brown
90-2450 Ivory
Medium Base
Keyless Current Tap
660W-125V



90-1121 Brown
90-2465 Ivory
Single to Twin Lampholder
Overall Height 2 3/4" - Ext. 2"
660W Max. Total-250V

