



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A110L 110 CFM 1.3 Sones Fan/Light

Broan/Nutone LLC

Catalog Number	A110L
Manufacturer	Broan/Nutone LLC
Description	Bath Fan and Light, Ceiling Type; 9-1/4 Inch L X 10 Inch W X 5-3/4 Inch H Size; UL Approval; 120 Vac At 60 HZ Voltage Rating; 1.2 Ampere Current Rating; No Lamp Included; Incandescent Lamp Type; (1) 100 W Lamp Wattage; 110 CFM Air Flow Rate
Weight per unit	9.6 (lbs/each)
Product Category	Exhaust Fans

### Features

Air Flow Rate	110 CFM
Current Rating	1.2 AMPERE
Duct Shape	Round
Duct Size	4 INCH DIA
Grill Finish	White Polymeric
Grill Shape	Rectangular
Grill Size	11-7/16 Inch L x 12-1/8 Inch W
Housing Shape	Rectangular
Lamp Included	NO
Lamp Type	Incandescent
Lamp Wattage	(1) 100 W
Sound Level	1.3 SONES
Ventilation Area	105 Sq Ft (Bathroom)
Voltage Rating	120 VAC AT 60 HZ

### Dimensions and Weight

Size	9-1/4 Inch L x 10 Inch W x 5-3/4 Inch H
------	-----------------------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Additional Information	Duct Direction Horizontal; Packaging Quantity 1 per Carton
Commodity Description	Exhaust Fans
Description	110 CFM 1.3 SONES FAN/LIGHT
extra long description	CEILING TYPE; 9-1/4 INCH LENGTH X 10 INCH WIDTH X 5-3/4 INCH HEIGHT SIZE; UL, HVI APPROVAL; 120 VOLT AC 60 HERTZ VOLTAGE RATING; 1.2 AMP CURRENT RATING; YES LAMP INCLUDED; INCANDESCENT LAMP TYPE; 100 WATT LAMP WATTAGE; GALVANIZED STEEL HOUSING MATERIAL; 110 CFM AIR FLOW RATE; 4 INCH DIAMETER DUCT SIZE; 1.3 SONES SOUND LEVEL; 11-7/16 INCH LENGTH X 12-1/8 INCH WIDTH GRILL SIZE; POLYMERIC GRILL MATERIAL; ROUND DUCT SHAPE; WHITE GRILL FINISH; FLEX[™] BRAND
Long Description	BATH FAN AND LIGHT, CEILING TYPE; 9-1/4 INCH L X 10 INCH W X 5-3/4 INCH H SIZE; UL APPROVAL; 120 VAC AT 60 HZ VOLTAGE RATING; 1.2 AMPERE CURRENT RATING; NO LAMP INCLUDED; INCANDESCENT LAMP TYPE; (1) 100 W LAMP WATTAGE; 110 CFM AIR FLOW RATE
Product Type	Bath Fan and Light

## Manufacturer Information

Brand	Broan/Nutone LLC
GTIN	00026715235339
Manufacturers Part Number	A110L
UPC	026715235339

## Taxonomies, Classifications, and Categories

Category Description	FANS & HEATERS
Type	CEILING

## Packaging

Carton	1
Weight Per each	9.61

## Uses, Certifications, and Standards

Approval	UL
----------	----