



## Fittings and Brackets


### Z Shape Fittings




**CAT. NO. A209**  
For attaching "A" series channel.




**CAT. NO. B209**  
For attaching "B" series channel.



**CAT. NO. C209**  
For attaching "C" series channel.



**CAT. NO. CZ209**  
For attaching "A" back to back.




**CAT. NO. EZ209**  
For attaching "E" series channel.

#### ..... Standard Dimensions .....


- Hole Spacing: 1 3/16" From End
- Hole Spacing: 1 7/8" Centers
- Hole Size: 1" Diameter
- Material: 1 1/8" Width
- Material: 1/4" Thick

Standard Finish — GoldGalv<sup>®</sup>, unless otherwise stated.  
Add EG suffix for SilverGalv<sup>®</sup> Finish


### Wing Shape Fittings




**CAT. NO. A217**




**CAT. NO. A218**




**CAT. NO. AW204**




**CAT. NO. AW205 L**




**CAT. NO. AW205-R**




**CAT. NO. AW214**




**CAT. NO. AW219**




**CAT. NO. AW220**



**CAT. NO. AW224**



**CAT. NO. AW226**



**CAT. NO. AW228**


#### ..... Standard Dimensions .....

- Hole Spacing: 1 3/16" From End
- Hole Spacing: 1 7/8" Centers
- Hole Size: 1" Diameter
- Material: 1 1/8" Width
- Material: 1/4" Thick


Standard Finish — GoldGalv<sup>®</sup>, unless otherwise stated.  
Add EG suffix for SilverGalv<sup>®</sup> Finish

## Fittings and Brackets


### Z Shape Fittings




**CAT. NO. A209**  
For attaching "A" series channel.




**CAT. NO. B209**  
For attaching "B" series channel.



**CAT. NO. C209**  
For attaching "C" series channel.



**CAT. NO. CZ209**  
For attaching "A" back to back.




**CAT. NO. EZ209**  
For attaching "E" series channel.

#### ..... Standard Dimensions .....


- Hole Spacing: 1 3/16" From End
- Hole Spacing: 1 7/8" Centers
- Hole Size: 1" Diameter
- Material: 1 3/8" Width
- Material: 1/4" Thick

Standard Finish — GoldGalv<sup>®</sup>, unless otherwise stated.  
Add EG suffix for SilverGalv<sup>®</sup> Finish


### Wing Shape Fittings




**CAT. NO. A217**




**CAT. NO. A218**




**CAT. NO. AW204**




**CAT. NO. AW205 L**




**CAT. NO. AW205-R**




**CAT. NO. AW214**




**CAT. NO. AW219**




**CAT. NO. AW220**



**CAT. NO. AW224**



**CAT. NO. AW226**



**CAT. NO. AW228**

#### ..... Standard Dimensions .....

- Hole Spacing: 1 3/16" From End
- Hole Spacing: 1 7/8" Centers
- Hole Size: 1" Diameter
- Material: 1 3/8" Width
- Material: 1/4" Thick

Standard Finish — GoldGalv<sup>®</sup>, unless otherwise stated.  
Add EG suffix for SilverGalv<sup>®</sup> Finish