



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

303 East Harned Avenue  
74075-0000, OK Stillwater  
Phone: 405-880-8633  
Fax: 405-880-8634



## A515M 15 Min Twist Timer Ivory

*Nsi Industries*

Catalog Number	A515M
Manufacturer	Nsi Industries
Description	The Tork A515M 15-Minute Spring-Wound In-Wall Twist Timer Is Designed to Control A Variety Of Indoor Appliances and Lights. Automate Your Home or Office to Save Energy and Money Using The Simple Twist Knob and Reliable Mechanical Timekeeping. Fits Into A Standard Electrical Box For In-Wall Mounting. Designed For Indoor Loads Such As Lights, Whole House Fans, Air Compressors, Water Heaters or Motors.
Weight per unit	0.4000 (lbs/each)
Product Category	Electromechanical Time Switches

### Features

action	SPDT
Base	Wall Plate
Contact Rating	125-250-277 VAC
Phase	Single Phase
Poles	1
Timing Range	15 Minute

### Dimensions and Weight

Size	H=5.00 - W=3.00
------	-----------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

303 East Harned Avenue  
74075-0000, OK Stillwater  
Phone: 405-880-8633  
Fax: 405-880-8634

## Descriptions

Description	15 MIN TWIST TIMER IVORY
extra long description	TORK A515M 15 Minute Spring Wound T
Features	The TORK A515M spring-wound in-wall twist timer carries our legacy of innovation and quality with reliable timekeeping and consistent performance. Use twist timers to set a countdown for automatically shutting off appliances or lighting, saving you energy and trouble. No more forgetting to turn off a garage light or attic fan: with a twist timer, simply wind the knob to the correct duration and automate the process. TORK twist timers are at home in residential environments or a range of commercial applicat
Long Description	The TORK A515M 15-Minute Spring-Wound In-Wall Twist Timer is designed to control a variety of indoor appliances and lights. Automate your home or office to save energy and money using the simple twist knob and reliable mechanical timekeeping. Fits into a standard electrical box for in-wall mounting. Designed for indoor loads such as lights, whole house fans, air compressors, water heaters or motors.
Product Type	15 Minute Spring Wound Twist Timer 125-277V SPDT Ivory
Special Features	Ivory 15 Minute No Hold In Wall Time Switch

## Manufacturer Information

Brand	TORK
GTIN	00786261150134
Manufacturers Part Number	A515M
UPC	786261150134

## Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
Type	Spring Wound In Wall Time Switch

## Packaging

Carton	1
Weight Per each	0.4

## Uses, Certifications, and Standards

Application	NSI
Enclosure	Single Gang Wall Plate
environmental conditions	32-122 F
Frequency Rating	50-60 Hz
Mounting	Single Gang Wall Plate
Operating Temperature	32-122 F
standard	cULus