



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A6K30R 600V 30A RK1 Fuse

Mersen Fuses

Catalog Number	A6K30R
Manufacturer	Mersen Fuses
Description	Fuse A6K-R - Class RK1 - Fast-Acting 600VAC 300VDC 30A Ferrule Amp-Trap®
Weight per unit	0.1800 (lbs/each)
Product Category	Current Limiting

Features

AC Voltage Rating	600
amperage rating	30
class	Class RK1
connection	Ferrule
DC Voltage Rating	300
interrupt rating	200
Voltage Rating	600

Material, Color, and Finish

Body Material	PolyTube
---------------	----------

Dimensions and Weight

Size	5 x 0.81
------	----------

Descriptions

Description	600V 30A RK1 FUSE
extra long description	Mersen A6K30R Fuse A6K-R - Class RK
Features	Current-limiting Amp-Trap A6K-R fuses provide excellent protection where high available short-circuit currents exist. These fast-acting fuses are particularly good for branch/feeder circuits and back-up protection.
Long Description	Fuse A6K-R - Class RK1 - Fast-Acting 600VAC 300VDC 30A Ferrule Amp-Trap®
Product Type	Fuse A6K-R - Class RK1 - Fast-Acting 600VAC 300VDC 30A Ferru
Short Description	600V 30A RK1 FUSE
Special Features	Rejection style design prevents replacement by other fuse classes Fiberglass body provides dimensional stability in harsh industrial environments Easy-to-read imprint label for quick recognition and replacement High degree of current limitation for low peak let-thru current



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Mersen
GTIN	00782001915605
Manufacturers Part Number	A6K30R
UPC	782001915605

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	CLASS RK1

Packaging

Carton	1
Package	10
Weight Per each	0.18

Uses, Certifications, and Standards

Application	Load centers Panelboards Switchboards Bus duct Feeder circuits Non-inductive loads Lighting circuits
Mounting standard	Clip UL listed to standard 248-12 File E2137 CSA certified to standard C22.2 No. 248.12 Self-certified for DC per UL248