



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AH360P6W Plug Pin&Sleeve 60A 250V 2P3W WT BL

*Eaton Wiring Devices*

|                  |   |
|------------------|---|
| Catalog Number   | AH360P6W  |
| Manufacturer     | Eaton Wiring Devices  |
| Description      | Eaton Arrow Hart Pin and Sleeve Plug, IP69K Rated, #8 - #2 Awg, #10 - #2 Awg (Ground), #12 - #16 Awg (Pilot), 60A, 250V, Back Wire, Blue, Nickel Plated Brass, IP67, Nylon, 2-Pole, 3-Wire, Grounding, 0.66-1.5IN (1.68-3.81CM), Male |
| Weight per unit  | 24.0 (lbs/each)   |
| Product Category | Pin & Sleeve Devices  |

### Features

|                 |                                    |
|-----------------|------------------------------------|
| amperage rating | 60                                 |
| connection      | Pin & Sleeve                       |
| dimensions      | 11.5000 IN X 5.1250 IN X 5.1250 IN |
| Material        | Nylon                              |
| media           | Yes                                |
| Phase           | 1                                  |
| Poles           | 2                                  |
| Voltage Rating  | 250V/AC                            |
| Wire Size       | 0.66-1.5                           |

### Material, Color, and Finish

|       |             |
|-------|-------------|
| Color | Blue & Gray |
|-------|-------------|

### Dimensions and Weight

|      |                      |
|------|----------------------|
| Size | 11.5 x 5.125 x 5.125 |
|------|----------------------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | PLUG PIN&SLEEVE 60A 250V 2P3W WT BL  |
| extra long description | EWD AH360P6W Plug Pin&Sleeve 60A 25  |
| Features               | Eaton's Arrow Hart full line of pin and sleeve devices offer sturdy nylon construction, rugged design with corrosion resistant components for lasting electrical performance, and watertight sealing that provides IP69K protection so you can feel confident in even the most severe washdown environments. |
| Long Description       | Eaton Arrow Hart pin and sleeve plug, IP69K Rated, #8 - #2 AWG, #10 - #2 AWG (Ground), #12 - #16 AWG (Pilot), 60A, 250V, Back wire, Blue, Nickel plated brass, IP67, Nylon, 2-pole, 3-wire, grounding, 0.66-1.5in (1.68-3.81cm), Male  |
| Product Type           | Plug Pin&Sleeve 60A 250V 2P3W WT BL  |
| Special Features       | Watertight P&S plugs   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00040893622910 |
| Manufacturers Part Number | AH360P6W       |
| UPC                       | 040893622910   |

## Taxonomies, Classifications, and Categories

|                      |                      |
|----------------------|----------------------|
| Category Description | Pin & Sleeve Devices |
| Type                 | Pin and Sleeve plug  |

## Availability

|        |          |
|--------|----------|
| Status | Inactive |
|--------|----------|

## Packaging

|                 |    |
|-----------------|----|
| Carton          | 1  |
| Package         | 12 |
| Weight Per each | 24 |

## Uses, Certifications, and Standards

|                          |   |
|--------------------------|---|
| Application              | Ind Facilities & Factories - Facility: Power Distribution and Control |
| environmental conditions | IP67 & IP69k  |
| Mounting                 | Cable   |
| standard                 | cRUus   |