

## Product Fuse Directory

MODEL	PART NUMBER	FUSE TYPE
RS-1007	FP500	0.5A/1000V, 6.3X32mm
RS-3 PRO	FP500	0.5A/1000V, 6.3X32mm
AM-250	FP650	630mA/500V, 6X32mm
	FA-12.5A/500V	12.5A/500V, 6X32mm
AM-270	FP160	10A/600V, 10X38mm
	FUSE-1A	1A/600V, 10X38mm
AM-500	FA-0.5A/700V	0.5A/700V, 6.3X32mm
	FP400	10A/600V, 6.3X25 mm
AM-510	FP500	0.5A/1000V, 6.3X32mm
	FP400	10A/600V, 6.3X25 mm
AM-520	FP500	0.5A/1000V, 6.3X32mm
	FP410	11A/1000V, 10X38mm
AM-530	FP500	0.5A/1000V, 6.3X32mm
	FP410	11A/1000V, 10X38mm
AM-560	FP500	0.5A/1000V, 6.3X32mm
	FP410	11A/1000V, 10X38mm
AM-570	FP500	0.5A/1000V, 6.3X32mm
	FP410	11A/1000V, 10X38mm
AM-140-A	FP160	10A/600V, 10X38mm
	FUSE-1A	1A/600V, 10X38mm
AM-160-A	FP412	0.44A/1000V, 10X38mm
	FP410	11A/1000V, 10X38mm
AM-220	5X20-250.5	0.5A/250V, 5X20mm
	6X32-250V10A	10A/250V, 6X32mm
AM-240	5X20-250.5	0.5A/250V, 5X20mm
	6X32-250V10A	10A/250V, 6X32mm
30XR-A	FP160	10A/600V, 10X38mm
	FP375	0.25A/700V, 6.3X32mm
33XR-A	FP100	10A/1000V, 10X3 8mm
	FP300	0.315A/1000V, 6.3X32mm
34XR-A	FP100	10A/1000V, 10X38mm
	FP300	0.315A/1000V, 6.3X32mm
37XR-A	FP100	10A/1000V, 10X38mm
	FP500	0.5A/1000V, 6.3X32mm
38XR-A	FP100	10A/1000V, 10X38mm
	FP500	0.5A/1000V, 6.3X32mm
5XP-A	FP300	0.315A/1000V, 6.3X32mm
15XP-B	FP200	2A/1000V, 6.3X32mm
35XP-A	FP200	2A/1000V, 6.3X32mm
HD110C	FP700	2A/1500V, 8X65mm
HD160C	FP700	2A/1500V, 8X65mm
DM7C	FP900	200mA / 700V, 6.3X32mm
DM9C	FA-6X32/.63	0.63A/500V, 6X32mm
	FP540	10A/600V, 6.3X32 mm
PRM-4	FP900	200mA/700V, 6.3X32mm
AMB-45	FA-0.5A/700V	0.5A/700V, 6.3X32mm
S2600	380.25-6X32	0.25A/380V, 6X32mm
T-100,T-300 (CT-100, 326B)	3AG-312.250	0.25A/250V, 6.3X32mm
T2200 (AT-200X)	2502-6X32	2A/250V, 6X32mm
X1000 (AT1000)	380.25-6X32	0.25A/380V, 6X32mm
CR50A	FP125	0.1A/250V, 5X20mm
LCR55A	FP125	0.1A/250V, 5X20mm
AU92	FP520	0.5V/500V, 6.3X32 mm
	FP540	10A/600V, 6.3X32 mm

# Product Fuse Directory and Software

## Software and Cables

Transfer measurement data to your computer with these kits.

For complete details on Amprobe software and to download the latest versions, please visit ([www.amprobe.com/softwaredownloads.html](http://www.amprobe.com/softwaredownloads.html))

## Download Suite Software

Download Suite is a free software package compatible with most of the Amprobe instruments with download capabilities. Enjoy the benefits of this powerful software package for a wide selection of Amprobe megohmmeters, ground resistance testers, multitesters, and power quality recorders.

- Install software once and use it with all supported Amprobe products
- All instruments share the same file format. You can open files recorded by you, other people, or the Amprobe instruments right on your PC.
- Download Suite automatically checks your version for upgrades and keeps your version current.
- Windows 95/ 98/ NT/ ME/ 2k/ XP/ 7/ 8/ 8.1/ 10 (32-bit and 64-bit) compatible

## USB-KIT2

- Download software with connection cable for Amprobe clamp meters

## USB-KIT3

- Download software with connection cable for Amprobe multimeters

## RS-USB, USB to RS-232 Adapter

- Converts the USB port of a PC to RS-232
- Supports Windows 95 (OSR2X), 98, 2000, ME, XP, Vista, Mac 8.6 and higher
- Works with Amprobe instruments with download capabilities
- Works with many other products with USB ports, including cameras, Palm Pilot, card readers, mouse, security systems, etc.
- Frees up the serial port for other uses

## TM-SWA, USB Cable and Software

- Allows for real-time data downloads from TMA10A and TMD90A
- Records two channels simultaneously



USB-KIT2



USB-KIT3



TM-SWA