



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AR642 60A Pin & Sleeve Recpt 3W 4P 250VDC/600vac *Crouse-Hinds*

Catalog Number	AR642
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Arktite Ar Receptacle, 60A, Three-Wire, Four-Pole, 50-400 HZ, Style 2, Copper-Free Aluminum, Spring Door, 600 Vac/250 VDC
Weight per unit	2.7 (lbs/each)
Product Category	Pin & Sleeve Devices

### Features

dimensions	4.2500 IN X 4.2500 IN X 4.2500 IN
insulation	Fiberglass-Reinforced Polyester
Voltage Rating	600 VAC AT 50 TO 400 HZ, 250 VDC
Wire Size	6 To 4 AWG (Building), 8 To 4 AWG (Extra Flex)

### Dimensions and Weight

Height	5-1/4
Width	4-1/4

### Descriptions

Description	60A PIN & SLEEVE RECPT 3W 4P 250VDC/600VAC
extra long description	CRS-H AR642 60A 3W4P ARKTE RCPT HOU
Features	Crouse-Hinds series Arktite plugs and receptacles are used to supply power to portable electrically operated devices, such as motor generator sets, compressors, heating and cooling units, welders, conveyors, lighting systems and similar equipment. Also used where temporary power is needed, such as at trailers, building units, heavy machinery or wherever electrical loads must be quickly disconnected from power source.
Long Description	Eaton Crouse-Hinds series Arktite AR receptacle, 60A, Three-wire, four-pole, 50-400 Hz, Style 2, Copper-free aluminum, Spring door, 600 Vac/250 Vdc
Product Type	60A 3W4P Arkte RCPT Hous SPDR
Special Features	Watertight, Grounding Style 2, NEMA 4 Enclosure, Reverse Interior

### Manufacturer Information

Brand	Eaton
GTIN	00782274062709
Manufacturers Part Number	AR642
UPC	782274062709



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... Pin & Sleeve Devices

Type ..... RECEPTACLE

## Packaging

Carton ..... 1

Weight Per each ..... 2.7

## Uses, Certifications, and Standards

Application ..... Ind Facilities & Factories - Facility: Power Distribution and Control

standard ..... UL 514, UL 1010, UL 1682, CSA C22.2