



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## B2209PAZN BLTF 3/4" Zinc Plate Pre-Assembled Unv Pipe Clamp

*Cooper B-Line/Cable Tray*

Catalog Number	B2209PAZN
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Multi-Grip/Offset Pipe Clamp, 0.0677" H X 2.3750" L X 1.25" W, Steel, 400 LBS Load, Pipe Clamp For Thinwall (Emt)
Weight per unit	0.1200 (lbs/each)
Product Category	Channel & Strut Fittings

### Features

dimensions	2.3750 IN X 1.2500 IN X 0.0677 IN
Material	14 Gauge Low Carbon Steel

### Material, Color, and Finish

Finish	Pre-Galvanized
--------	----------------

### Dimensions and Weight

Size	3/4 in
------	--------

### Descriptions

Construction	TWO PIECE
Description	BLTF 3/4" ZINC PLATE PRE-ASSEMBLED UNV PIPE CLAMP
extra long description	B-LINE B2209PAZN 3/4"-MULTI-GRIP PI
Features	Eaton offers a wide variety of B-Line series pipe clamps and accessories used for the support and attachment of pipe to structural members.
Long Description	Eaton B-Line series multi-grip/offset pipe clamp, 0.0677" H x 2.3750" L x 1.25" W, Steel, 400 Lbs load, Pipe clamp for thinwall (EMT)
Product Type	3/4"-Multi-Grip Pipe Clamp, Pre-Asm, Thinwal
Special Features	Includes Combination Recess Hex Head Machine Screw and Square Nut, Pipe Range 0.917 To 1.081 In OD, Load Capacity 400 Lb Vertical, 50 Lb Transverse

### Manufacturer Information

Brand	Eaton
GTIN	00781011604240
Manufacturers Part Number	B2209PAZN
UPC	781011604240

### Taxonomies, Classifications, and Categories

Category Description	BEAM, RA, EDGE, & PARALLEL CLAMPS
Type	Multi-grip and offset pipe clamp



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	100
Weight Per each	0.12

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Mounting	CHANNEL
standard	Not Applicable